

	<p>These two Noga Burr Tools offer the solution to most deburring requirements Both tools are based on the NG-1 Noga Burr handle which will accept all S Type heavy duty blades</p> <p>Noga Burr 3 is supplied with 1 x S10, S20 and S35 blade</p> <p>Noga Burr 5 is supplied with 1 x S10, S20, S35, S101 and S202 blades</p> <p>See Handle and Blade details below</p>
---	--

Packed Weight and Dimensions

Code	Description	Weight g	W mm	H mm	L mm
NG 1003	Noga Burr 3	53	31	31	153
NG 1005	Noga Burr 5	58	32	32	153

	<p>Instructions</p> <p>Do not use heavy pressure when deburring as this will cause the blade to dig into the material and give an uneven finish Use light and even pressure which will allow the blade and handle to work together to remove the burr and leave a smooth finish on the component</p> <p>Blades should be handled carefully as they are sharp and can cut Blades can break causing flying objects Sharp edges and flying objects can cause injury Users and bystanders should wear protective safety glasses Do not pry or bend blades Keep blades and sharp tools away from children Do not regrind blades as this will weaken the blade and cause breakage and possible injury</p> <p>All Noga products meet the strict requirements of ISO 9001 and ISO 14001</p>
--	--


NG-1 Handle


	<p>NG-1 Handle accepts all “S” type Blades Ergonomic soft grip, acetyl and rubber construction Removable end cap for blade storage 125mm long x 28mm maximum diameter Blades are secured by pulling back the front locking mechanism and are free to rotate</p>
---	---

Packed Weight and Dimensions


Code	Description	Weight g	W mm	H mm	L mm
NG1000	NG-1 Handle	45	32	32	153


S10 Heavy Duty Deburring Blade

	Order Code	S10				
	Pack Reference	BS1010				
	Cutting	Right Hand				
	Works best on	Steel, Aluminium and Plastic				
	Used with Handle	NG-1, NG-3 + S Holder, Plastic Edge Off, Rapid Burr, Plastic Rapid Burr,				
Packed Weight and Dimensions						
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm	
S10	10	40	65	8	83	


	Order Code	S10
	Included Angle	40°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	48mm
	L1: Length Inside Handle	28mm
	L2: Protrusion from Handle Length	20mm
L3: Cutting Length	6mm	
D: Shank Diameter	3.2mm	


S20 Heavy Duty Deburring Blade

	Order Code	S20				
	Pack Reference	BS2010				
	Cutting	Left and Right Hand				
	Works best on	Brass and Cast Iron				
	Used with Handle	NG-1, NG-3 + S Holder, Plastic Edge Off, Rapid Burr, Plastic Rapid Burr,				
Packed Weight and Dimensions						
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm	
S20	10	40	65	8	83	


	Order Code	S20
	Included Angle	60°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	48mm
	L1: Length Inside Handle	28mm
	L2: Protrusion from Handle Length	20mm
L3: Cutting Length	6mm	
D: Shank Diameter	3.2mm	


S35 Heavy Duty Deburring Blade

	Order Code	S35				
	Pack Reference	BS3510				
	Cutting	Left and Right Hand				
	Works best on	Straight Edges on most materials				
	Used with Handle	NG-1, NG-3 + S Holder, Plastic Edge Off, Rapid Burr, Plastic Rapid Burr,				
Packed Weight and Dimensions						
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm	
S35	10	40	65	8	83	


	Order Code	S35
	Included Angle	55°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	48mm
	L1: Length Inside Handle	28mm
	L2: Protrusion from Handle Length	20mm
	L3: Cutting Length	7mm
D: Shank Diameter	3.2mm	


S101 Heavy Duty Deburring Blade

	Order Code	S101				
	Pack Reference	BK1010				
	Cutting	Right Hand				
	Works best on	Fine Edges on all materials				
	Used with Handle	NG-1, NG-3 + S Holder, Plastic Edge Off, Rapid Burr, Plastic Rapid Burr,				
Packed Weight and Dimensions						
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm	
S101 LH	10	40	65	8	83	

	Order Code	S101
	Included Angle	40°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	44mm
	L1: Length Inside Handle	28mm
	L2: Protrusion from Handle Length	16mm
	L3: Cutting Length	7mm
D: Shank Diameter	3.2mm	

S202 Heavy Duty Deburring Blade

	Order Code	S202				
	Pack Reference	BK2010				
	Cutting	Left and Right Hand				
	Works best on	Brass and Cast Iron Fine Edges				
	Used with Handle	NG-1, NG-3 + S Holder, Plastic Edge Off, Rapid Burr, Plastic Rapid Burr,				
Packed Weight and Dimensions						
Code	Pack Quantity	Weight g	Wmm	Hmm	Lmm	
S202	10	40	65	8	83	

	Order Code	S202
	Included Angle	55°
	Blade Material	HSS M2
	Blade Hardness	62 – 64 HRC
	L: Overall Length	44mm
	L1: Length Inside Handle	28mm
	L2: Protrusion from Handle Length	16mm
	L3: Cutting Length	7mm
	D: Shank Diameter	3.2mm