

Programmable DC Power Supply

Single Channel, 0-30V, 0-10A



**RoHS
Compliant**



Features:

- Input Voltage : 230V
- Complete digital control / programmable
- 10mV / 1mA resolution
- Low noise and ripple
- CV / CC constant voltage and constant current modes
- Settable OCP and OVP, constant protection mode
- 5 sets of parameters can be stored and recalled
- Output switch control
- Power-off memory function
- Keyboard lock function to prevent operator errors
- Interfaces on programmable models : RS232, USB
- Easy alternative to the traditional digital-display power supplies
- Certified by CE

Specifications:

Voltage Range / Current Range	0-30V / 0-10A
Load Regulation	Voltage : $\leq 0.01\%$ +2mV / Current : $\leq 0.1\%$ +5mA
Line Regulation	Voltage : $\leq 0.01\%$ +3mV / Current : $\leq 0.1\%$ +3mA
Setup Resolution	Voltage : 10mV / Current : 1mA
Setting accuracy (25°C $\pm 5^\circ\text{C}$)	Voltage : $\leq 0.5\%$ +20mV / Current : $\leq 0.5\%$ +10mA
Ripple (20hz - 20M)	Voltage : $\leq 2\text{mVrms}$ / Current : $\leq 5\text{mArms}$
Temperature Coefficient	Voltage : $\leq 100\text{ppm}$ +10mV / Current : $\leq 100\text{ppm}$ +5mA
Read Back Accuracy	Voltage : 10mV / Current : 1mA
Read Back Temperature Coefficient	Voltage : $\leq 100\text{ppm}$ +10mV / Current : $\leq 100\text{ppm}$ +5mA
Reaction Time (10% Rated load)	Voltage : $\leq 100\text{mS}$ / Current : $\leq 100\text{mS}$
Operation Environment	Indoor use Altitude: $\leq 2,000\text{m}$ Ambient temperature 0 ~ 40°C Relative humidity $\leq 80\%$
Interfaces	Optional Interfaces (for programmable models only) : RS232, USB
Accessories	User manual, Power cord (1.2M), USB cord (1.2M; for programmable models only)
Weight and Dimension	7.2 kg / 110mm(W) \times 156mm(H) \times 310mm(D)
Storage Environment	Ambient temperature -10°C to +70°C Relative humidity : $\leq 70\%$

Part Number Table

Description	Part Number
Programmable DC Power Supply, Single Channel, 0-30V, 0-10A	72-2930

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

