

## ADNB-C Series

60 Watts

### Data Sheet

**Total Power:** 60 Watts  
**Input Voltage:** 88 - 264 Vac  
 124 - 370 Vdc  
**# of Outputs:** Single

### SPECIAL FEATURES

- Universal input 88 - 264 Vac
- High efficiency 88% typical
- Full power at 50 °C
- Adjustable output voltage
- Overvoltage protection
- Overload protection
- LED for output
- Screw terminal connections
- RoHS compliant
- No tools required for mounting
- Three year warranty

### SAFETY\*

- UL508
- UL1310 Class 2
- TÜV EN60950-1
- CE

\*AC input only



### Electrical Specifications

Input	
AC input range	Nominal: 88 - 264 Vac
DC input range	124 - 370 Vdc
Frequency	47 - 63 Hz
Efficiency	88%
Inrush current (typical)	< 30 A (115 Vac) or <60 A (230 Vac)
Output	
Nominal voltage	12 V, 15 V, 24 V, 48 V
Initial voltage setting	1%
Hold-up time	> 16 ms (115 Vac), > 32 ms (230 Vac) at full load
Voltage regulation	± 1% line regulation; ± 1% load regulation
Ripple	180 mV p-p
Overload protection	> 102% of rated output current, auto recovery
Overvoltage protection	115% of Vo nominal, auto recovery
Time and temperature drift	< 0.03%

### General Specifications

EMC emissions	EN55022 Radiated and Conducted Class B
EMC standard	EN61000-3-2; 2006 Class A, EN61000-3-3: 1995 + A1: 2001 + A2: 2005 EN61204-3: 2000, EN55024: 1998 + A1: 2001 + A2: 2003 light industry level, criteria A
Warranty	3 Years
Status indicators	Visual: DC ON (LED)

### Environmental Specifications

Storage temperature	-40 °C to + 85 °C
Operating temperature	From -20 °C to 70 °C. Derate starting at 50 °C
Vibration	0-500 Hz, 2 G 10 min/1 cycle, along X, Y, Z each axis, 60 min for each axis

### Other Features

External fusing	Not required. Unit provides internal fuse (not accessible)	
Mounting orientation	Standard: Vertical Simple snap-on to DIN TS35/7.5 or TS35/15 rail system	
Ventilation	Normal convection, No fan required	
Cooling spacing	All models	All sides, 25 mm free space
Connections	Input/Output: Screw terminals, 24-10 AWG (0.2 – 4 mm <sup>2</sup> ) for flexible/solid cable, Input connector can withstand torque at maximum 9 pound-inches. Output connector can withstand torque at maximum 5.5 pound-inches 8 m/m stripping at cable end recommends	


### Ordering Information

Model Number	Power	Input Voltage	Weight	Output	Efficiency	MTBF
						MIL-HDBK-217F
ADNB050-12-1PM-C	60 W	88 - 264 Vac 124 - 370 Vdc	0.66 lbs (300 g)	12 V @ 5 A	79%	407.1 KHrs
ADNB040-15-1PM-C	60 W	88 - 264 Vac 124 - 370 Vdc	0.66 lbs (300 g)	15 V @ 4 A	86%	407.1 KHrs
ADNB025-24-1PM-C	60 W	88 - 264 Vac 124 - 370 Vdc	0.66 lbs (300 g)	24 V @ 2.5 A	89%	407.1 KHrs
ADNB012-48-1PM-C	60 W	88 - 264 Vac 124 - 370 Vdc	0.66 lbs (300 g)	48 V @ 1.25 A	89%	407.1 KHrs

### Dimensions

	Height	Width	Depth
ADNB050-12-1PM-C	3.54 in (90 mm)	1.57 in (40 mm)	3.9 in (99 mm)
ADNB040-15-1PM-C	3.54 in (90 mm)	1.57 in (40 mm)	3.9 in (99 mm)
ADNB025-24-1PM-C	3.54 in (90 mm)	1.57 in (40 mm)	3.9 in (99 mm)
ADNB012-48-1PM-C	3.54 in (90 mm)	1.57 in (40 mm)	3.9 in (99 mm)

### Mechanical Drawing



install DIN rail TS-35 / 7.5 or TS-35 / 15

Unit : mm / inch

### WORLDWIDE OFFICES

#### Americas

2900 S.Diablo Way  
Tempe, AZ 85282  
USA  
+1 888 412 7832

#### Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
+44 (0) 1384 842 211

#### Asia (HK)

14/F, Lu Plaza  
2 Wing Yip Street  
Kwun Tong, Kowloon  
Hong Kong  
+852 2176 3333



[www.artesyn.com](http://www.artesyn.com)

Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2016 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit [www.artesyn.com/legal](http://www.artesyn.com/legal).

For more information: [www.artesyn.com/power](http://www.artesyn.com/power)  
For support: [productsupport.ep@artesyn.com](mailto:productsupport.ep@artesyn.com)