

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191600012**
Status: **Active**
Overview: Splices
Description: Closed-End Insulated Splice for 14-22 AWG Wire, Clear

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series 19160
Crimp Quality Equipment Yes
Mil-Spec N/A
MolexKits Yes
Overview Splices
Product Name Closed-End Insulated
UPC 800753110229

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.472/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 6.10mm max.
Wire Size AWG 14, 16, 18, 20, 22

Electrical

Voltage - Maximum 300V

Material Info

Old Part Number NC-2214

Reference - Drawing Numbers

Packaging Specification PK-19408-109
Product Specification PS-19902-013
Sales Drawing SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

19160 Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Hand Crimp Tool	0640010600
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050600
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	0640053400

This document was generated on 04/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION