Product data sheet Characteristics

XB5AA21

black flush complete pushbutton Ø22 spring return 1NO unmarked

Main	
Commercial Status	Commercialised
Range of product	Harmony XB5
Product or component type	Complete pushbutton
Device short name	XB5
Bezel material	Plastic
Fixing collar material	Plastic
Mounting diameter	22 mm
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Black flush unmarked
Contacts type and composition	1 NO
Contacts operation	Slow-break
Connections - terminals	Screw clamp terminals: 1 x 0.222 x 2.5 mm² without cable end conforming to EN/IEC 60947-1 Screw clamp terminals: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1

Complementary

Complementary					
Height	42 mm				
Width	30 mm				
Depth	52 mm				
Terminals description ISO n°1	(13-14)NO				
Product weight	0.037 kg				
Resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m				
Contacts usage	Standard contacts				
Positive opening	Without positive opening				
Operating travel	4.3 mm (total travel) 2.6 mm (NO changing electrical state)				
Operating force	3.8 N (NO changing electrical state)				
Mechanical durability	5000000 cycles				
Tightening torque	0.81.2 N.m conforming to EN 60947-1				
Shape of screw head	Slotted head compatible with flat \emptyset 5.5 mm screwdriver Slotted head compatible with flat \emptyset 4 mm screwdriver Cross head compatible with pozidriv No 1 screwdriver Cross head compatible with Philips no 1 screwdriver				
Contacts material	Silver alloy (Ag/Ni)				
Short circuit protection	10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1				
[lth] conventional free air thermal current	10 A conforming to EN/IEC 60947-5-1				
[Ui] rated insulation voltage	600 V (degree of pollution: 3) conforming to EN/IEC 60947-1				
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1				
[le] rated operational current	1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1				

Electrical durability	1000000 cycles, DC-13, 0.5 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A at 24 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A at 120 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 2 A at 230 V, operating rate: 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C
Electrical reliability IEC 60947-5-4	Λ < 10exp(-8) at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4 Λ < 10exp(-6) at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4

Environment

Protective treatment	TH				
Ambient air temperature for storage	-4070 °C				
Ambient air temperature for operation	-2570 °C				
Class of protection against electric shock	Class II conforming to IEC 60536				
IP degree of protection	IP66 conforming to IEC 60529				
NEMA degree of protection	NEMA 4X NEMA 13				
IK degree of protection	IK03 conforming to IEC 50102				
Standards	CSA C22-2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 UL 508				
Product certifications	BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL listed				
Vibration resistance	5 gn (f = 2500 Hz) conforming to IEC 60068-2-6				
Shock resistance	50 gn for 11 ms half sine wave acceleration conforming to IEC 60068-2-27 30 gn for 18 ms half sine wave acceleration conforming to IEC 60068-2-27				

Contractual warranty


Period	18 months
--------	-----------



Product data sheet Dimensions Drawings

XB5AA21


Dimensions



- e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.
- (1) Additional row of contacts or double contact

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. Ø22.5 mm recommended (Ø22.3 $_0$ $^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 in. $_0$ $^{+0.016}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- (1) Diameter on finished panel or support
- For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- Ø22.5 mm recommended (Ø22.3 $_0$ ^{+0.4}) / Ø0.89 in. recommended (Ø0.88 in. $_0$ ^{+0.016})