

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0709282001](#)
Status: **Active**
Overview: [LFH™ Interconnect System](#)
Description: 1.27mm Pitch LFH™ Matrix 50 Receptacle, Shielded, Right Angle, 2.34mm PC Tail Length, Screw Hole M3 Thread, Gold Plating, 60 Circuits

Documents:

3D Model	Test Summary TS-70928-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-70928 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	70928
Application	Board-to-Board, Wire-to-Board
Comments	Dim.B for 1.00mm max. Panel Thickness is 9.65mm and 10.67mm for 1.63mm max. Panel Thickness
Component Type	Receptacle
MolexKits	Yes
Overview	LFH™ Interconnect System
Product Name	LFH™
Type	N/A
UPC	800753641150

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Receptacle
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	7.038/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	2.34mm
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[70928](#) Series

Mates With

[70929](#) LFH™ Plug

Use With

[71628](#) Guide Pin, Guide Sleeve [71629](#) or
[71771](#), [70982](#) Hex Screw Kit

Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	40V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	040
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	245
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-70928, RPS-70928-001, RPS-70928-002
Sales Drawing	SDA-70928-20**
Test Summary	TS-70928-001

This document was generated on 04/07/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION