

SOT-26



Pin Definition:

- | | |
|----------|-----------|
| 1. Drain | 6. Drain |
| 2. Drain | 5. Drain |
| 3. Gate | 4. Source |

PRODUCT SUMMARY

V_{DS} (V)	$R_{DS(on)}$ (m Ω)	I_D (A)
30	30 @ $V_{GS} = 10V$	6.7
	42 @ $V_{GS} = 4.5V$	5.7

Features

- Advance Trench Process Technology
- High Density Cell Design for Ultra Low On-resistance

Application

- Load Switch
- PA Switch

Ordering Information

Part No.	Package	Packing
TSM3424CX6 RF	SOT-26	3Kpcs / 7" Reel
TSM3424CX6 RFG	SOT-26	3Kpcs / 7" Reel

Note: "G" denote for Halogen Free Product

Absolute Maximum Rating ($T_a = 25^\circ C$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current	I_D	6.7	A
Pulsed Drain Current	I_{DM}	30	A
Continuous Source Current (Diode Conduction) ^{a,b}	I_S	1.7	A
Maximum Power Dissipation	P_D	2.0	W
		1.3	
Operating Junction Temperature	T_J	+150	$^\circ C$
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 to +150	$^\circ C$


Thermal Performance

Parameter	Symbol	Limit	Unit
Junction to Case Thermal Resistance	$R_{\theta JC}$	30	$^\circ C/W$
Junction to Ambient Thermal Resistance (PCB mounted)	$R_{\theta JA}$	80	$^\circ C/W$

Notes:

- a. Pulse width limited by the Maximum junction temperature
b. Surface Mounted on FR4 Board, $t \leq 10$ sec.

Block Diagram



Electrical Specifications (Ta = 25°C unless otherwise noted)


Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Static ^a						
Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250μA	BV _{DSS}	30	--	--	V
Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	V _{GS(TH)}	1	1.4	3	V
Gate Body Leakage	V _{GS} = ±20V, V _{DS} = 0V	I _{GSS}	--	--	±100	μA
Zero Gate Voltage Drain Current	V _{DS} = 24V, V _{GS} = 0V	I _{DSS}	--	--	1.0	μA
On-State Drain Current	V _{DS} ≥ 5V, V _{GS} = 10V	I _{D(ON)}	30	--	--	A
Drain-Source On-State Resistance	V _{GS} = 10V, I _D = 6.7A	R _{DS(ON)}	--	23	30	mΩ
	V _{GS} = 4.5V, I _D = 5.7A		--	32	42	
Forward Transconductance	V _{DS} = 5V, I _D = 5.0A	g _{fs}	--	14	--	S
Diode Forward Voltage	I _S = 1.7A, V _{GS} = 0V	V _{SD}	--	0.76	1	V
Dynamic ^b						
Total Gate Charge	V _{DS} = 15V, I _D = 6.7A, V _{GS} = 10V	Q _g	--	4.52	--	nC
Gate-Source Charge		Q _{gs}	--	1.24	--	
Gate-Drain Charge		Q _{gd}	--	1.68	--	
Input Capacitance	V _{DS} = 15V, V _{GS} = 0V, f = 1.0MHz	C _{iss}	--	400.96	--	pF
Output Capacitance		C _{oss}	--	100.47	--	
Reverse Transfer Capacitance		C _{rss}	--	71.82	--	
Switching ^c						
Turn-On Delay Time	V _{DD} = 15V, R _L = 2.2Ω, I _D = 1A, V _{GEN} = 10V, R _G = 6Ω	t _{d(on)}	--	7.42	--	nS
Turn-On Rise Time		t _r	--	3.41	--	
Turn-Off Delay Time		t _{d(off)}	--	20.4	--	
Turn-Off Fall Time		t _f	--	3.01	--	

Notes:


a. pulse test: PW ≤ 300μS, duty cycle ≤ 2%

b. For DESIGN AID ONLY, not subject to production testing.

c. Switching time is essentially independent of operating temperature.




Switching Test Circuit




Switchin Waveforms

Electrical Characteristics Curve ($T_a = 25^\circ\text{C}$, unless otherwise noted)


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Gate Charge



On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage




Electrical Characteristics Curve ($T_a = 25^{\circ}\text{C}$, unless otherwise noted)


On-Resistance vs. Gate-Source Voltage




Threshold Voltage




Single Pulse Power



Normalized Thermal Transient Impedance, Junction-to-Ambient




SOT-26 Mechanical Drawing



SOT-26 DIMENSION						
DIM	MILLIMETERS			INCHES		
	MIN	TYP	MAX	MIN	TYP	MAX
A	0.95 BSC			0.0374 BSC		
A1	1.9 BSC			0.0748 BSC		
B	2.60	2.80	3.00	0.1024	0.1102	0.1181
C	1.40	1.50	1.70	0.0551	0.0591	0.0669
D	2.80	2.90	3.10	0.1101	0.1142	0.1220
E	1.00	1.10	1.20	0.0394	0.0433	0.0472
F	0.00	--	0.10	0.00	--	0.0039
G	0.35	0.40	0.50	0.0138	0.0157	0.0197
H	0.10	0.15	0.20	0.0039	0.0059	0.0079
I	0.30	--	0.60	0.0118	--	0.0236
J	5°	--	10°	5°	--	10°

Marking Diagram



24 = Device Code

Y = Year Code

M = Month Code

(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)

= Month Code for Halogen Free Product

(O=Jan, P=Feb, Q=Mar, R=Apl, S=May, T=Jun, U=Jul, V=Aug, W=Sep, X=Oct, Y=Nov, Z=Dec)

L = Lot Code

Not Recommended
TSM3424CX6 RF

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.