



Main

Commercial Status	Commercialised
Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal (ball bearing mounted)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	10...120 °C for high temperature -40...70 °C for low temperature -25...70 °C for standard environment
Ambient air temperature for storage	10...120 °C for high temperature -40...70 °C for low temperature -40...70 °C for standard environment
Environmental characteristic	High temperature Low temperature Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0905 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.