Product data sheet Characteristics

RSB2A080BD

interface plug-in relay - Zelio RSB - 2 C/O - 24 V DC - 8 A



Main Commercial Status Commercialised Range of product Zelio Relay Interface relay Series name Product or component Plug-in relay type RSB Device short name 2 C/O Contacts type and composition Contacts operation Standard Control circuit voltage 24 V DC [Ithe] conventional en-8 A at -40...40 °C closed thermal current

Status LED	Without
Control type	Without pushbutton
Sale per indivisible quantity	10

Complementary

Complementary		
Shape of pin	Flat Flat (PCB type)	
Average resistance	1440 Ohm (DC) at 20 °C +/- 10 %	
Rated operational voltage limits	19.226.4 V DC	
[Ui] rated insulation voltage	400 V conforming to EN/IEC 60947	
[Uimp] rated impulse withstand voltage	3.6 kV conforming to IEC 61000-4-5	
Contacts material	Silver alloy (Ag/Ni)	
[le] rated operational current	8 A, NO (AC-1/DC-1) conforming to IEC 4 A, NC (AC-1/DC-1) conforming to IEC	
Minimum switching current	5 mA	
Maximum switching voltage	400 V AC 300 V DC	
Minimum switching voltage	5 V	
Maximum switching capacity	224 W (DC) 2000 VA (AC)	
Minimum switching capacity	300 mW	
Operating rate	<= 72000 cycles/hour no-load <= 600 cycles/hour under load	
Mechanical durability	30000000 cycles	
Electrical durability	>= 100000 cycles for resistive load at 8 A, 250 V	
Operating time	9 ms between coil energisation and making of the On-delay contact 4 ms between coil de-energisation and making of the Off-delay contact	
Marking	CE	
Protection category	RTI	
Operating position	Any position	
CAD overall width	13 mm	
CAD overall height	29 mm	
CAD overall depth	20 mm	
Terminals description ISO n°1	(11-14-23)OC (21-22-24)OC (A1-A2)CO	
Product weight	0.014 kg	
·		

Resistive rated load	8 A at 28 V DC 8 A at 250 V AC
Average consumption in W	0.45 W DC
Drop-out voltage threshold	>= 0.1 Uc DC

Environment

Dielectric strength	5000 V AC between coil and contact	
2.0.004.0 04.01.94.	2500 V AC between poles	
	1000 V AC between contacts	
Standards	EN/IEC 61810-1	
	UL 508	
	CSA C22.2 No 14	
Product certifications	CSA	
	GOST	
	UL	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	10 gn +/- 1 mm (f = 10150 Hz)10 cycles conforming to EN/IEC 60068-2-6	
IP degree of protection	IP40 conforming to EN/IEC 60529	
Shock resistance	5 gn for11 ms in operation conforming to EN/IEC 60068-2-27	
	10 gn for11 ms not operating conforming to EN/IEC 60068-2-27	
Ambient air temperature for operation	-4085 °C (DC)	

Contractual warranty


Period	18 months	
--------	-----------	--



Product data sheet Dimensions Drawings

RSB2A080BD


Dimensions



Product data sheet Connections and Schema

RSB2A080BD


Wiring Diagram



Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

A RSB2A080••

B RSB1A160••


C RSB1A120••

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

A RSB2A080••

B RSB1A160••

C RSB1A120••