
125L Series

HAY, www.vishay.com

Vishay Cera-Mite

AC Line Rated Ceramic Disc Capacitors Class X1, 400 V_{AC} / Class Y4, 125 V_{AC}



QUICK REFERENCE DATA			
DESCRIPTION	VALUE		
Ceramic Class	2		
Ceramic Dielectric	Y5V		
Voltage (V _{AC})	125 400		
Min. Capacitance (pF)	1000		
Max. Capacitance (pF)	50 000		
Mounting	Radial		

INSULATION RESISTANCE

Min. 1000 ΩF

TOLERANCE ON CAPACITANCE

± 20 %

DISSIPATION FACTOR

2.0 % max. at 1 kHz; 1 V

CERAMIC DIELECTRIC

Y5V (Class 2)

CLIMATIC CATEGORY ACC. TO EN 60068-1 25/125/21

OPERATING TEMPERATURE RANGE

-30 °C to +125 °C

FEATURES

- Complying with IEC 60384-14 3rd edition
- High reliability
- Complete range of capacitance values
- Radial leads
- Singlelayer AC disc safety capacitors
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- X1, Y4 according to IEC 60384-14.3
- Across-the-line
- Line by-pass
- Antenna coupling

DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having a diameter of 0.032" (0.81 mm) or 0.025"(0.64 mm). The capacitors may be supplied with radial kinked or straight leads having a lead spacing of 0.375"(9.5 mm) or 0.250" (6.4 mm). The standard tolerance is ± 20 %. Coating is made of flame retardant epoxy resin in accordance with "UL 94 V-0".

CAPACITANCE RANGE

1.0 nF to 0.050 μF

RATED VOLTAGE

IEC 60384-14.3:

- X1: 400 V_{AC}, 50 Hz
- Y4: 125 V_{AC}, 50 Hz

DIELECTRIC STRENGTH BETWEEN LEADS

Component test: 2000 V_{AC}, 50 Hz, 2 s As repeated test admissible only once with: 1800 V_{AC}, 50 Hz, 2 s

Random sampling test (destructive test): 2000 V_{AC} , 50 Hz, 60 s

DIELECTRIC STRENGTH OF BODY INSULATION

2300 V_{AC}, 50 Hz, 60 s (destructive test)



RoHS

COMPLIAN[®]


1



www.vishay.com

Vishay Cera-Mite

DIMENSIONS in inches (millimeters)



ORDERING INFORMATION, CERAMIC X1 / Y4 CAPACITORS 125L								
C	TOL.	D _{max.} DIAMETER	T _{max.} THICKNESS	WIRE SIZE		LS LEAD SPACE	LO LEAD OFFSET	ORDERING
(pF)	(%)	INCH (mm)	INCH (mm)	AWG	AWG INCH (mm)	INCH (mm) ± 1 mm	INCH (mm) ± 0.5 mm	CODE
1000		0.330 (8.4)	0.195 (5.0)			0.250 (6.4)	0.094 (2.4)	125LD10-R
1500		0.330 (8.4)	0.195 (5.0)				0.098 (2.5)	125LD15-R
2000		0.330 (8.4)	0.188 (4.8)				0.091 (2.3)	125LD20-R
2200		0.330 (8.4)	0.182 (4.7)				0.083 (2.1)	125LD22-R
3300		0.365 (9.3)	0.195 (5.0)				0.094 (2.4)	125LD33-R
4700		0.400 (10.2)	0.185 (4.7)	20			0.087 (2.2)	125LD47-R
5000		0.430 (11.0)	0.195 (5.0)	20	0.032 (0.81)		0.094 (2.4)	125LD50-R
6800	± 20	0.490 (12.5)	0.198 (5.1)				0.098 (2.5)	125LD68-R
8200	± 20	0.530 (13.5)	0.193 (5.0)			32 (0.81)	0.094 (2.4)	125LD82-R
0.010 µF		0.560 (14.3)	0.195 (5.0)				0.098 (2.5)	125LS10-R
0.015 µF		0.720 (18.3)	0.205 (5.3)				0.102 (2.6)	125LS15-R
0.018 µF		0.790 (20.1)	0.205 (5.3)				0.106 (2.7)	125LS18-R
0.020 µF		0.720 (18.3)	0.250 (6.4)	22	22 0.025 (0.64) 20 0.032 (0.81) 22 0.025 (0.64)		0.087 (2.2)	125LS20-R
0.022 µF		0.790 (20.1)	0.192 (4.9)	20			0.094 (2.4)	125LS22-R
0.030 µF		0.720 (18.3)	0.240 (6.1)	22			0.087 (2.2)	125LS30-R
0.050 µF		0.925 (23.5)	0.275 (7.0)	22	0.025 (0.64)		0.087 (2.2)	125LS50-R

Notes

• Alternate lead spacings of 7.5 mm and 10 mm are available bulk or tape and reel on request.

• Minimum lead clearance according to IEC 60384-14: 0.118" (3 mm)

TAPE AND REEL OPTIONS

Part number codes and specifications for tape and reel packaging are found in the general information document - find web-link below.


2

125L Series


Vishay Cera-Mite





LEAKAGE CURRENT VS. VOLTAGE (Typical)




INSERTION LOSS VS. FREQUENCY (Typical)











Revision: 02-Mar-15

3 For technical questions, contact: <u>ceramitesupport@vishay.com</u> Document Number: 23106


THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

125L Series

SHA www.vishay.com

Vishay Cera-Mite

APPROVALS				
IEC 60384-14.3 - Safety tests This approval together with CB test certificate substitute	s all national approvals	i.		
CB Certificate				
Y4-capacitor: CB test certificate:	CA/13650/CSA	1 nF to 50 nF	125 V _{AC}	(CD)
X1-capacitor: CB test certificate:	CA/13650/CSA	1 nF to 50 nF	400 V _{AC}	U
VDE				^
Y4-capacitor: VDE marks approval:	40003976	1 nF to 50 nF	125 V _{AC}	$\sum \sqrt{\lambda}$
X1-capacitor: VDE marks approval:	40003976	1 nF to 50 nF	400 V _{AC}	DEF
DIN EN 60384-14 VDE 0565-1-1:2006-04 - Safety tests				
Underwriters Laboratories Inc.				
Y4-capacitor: UL test certificate:	E99264	1 nF to 50 nF	125 V _{AC}	
X1-capacitor: UL test certificate:	E99264	1 nF to 50 nF	400 V _{AC}	
UL 60384-14, CSA E60384-1:03, CSA E60384-14:09				G III II I
Fixed capacitors for electromagnetic interference suppre	ession and connection	to the supply mains.		



RELATED DOCUMENTS		
General Information	www.vishay.com/doc?23140	
CB Test Certificate	www.vishay.com/doc?22234	
VDE Marks Approval	www.vishay.com/doc?22235	
UL Test Certificate	www.vishay.com/doc?22236	



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.