

Product data sheet

Characteristics

9016GAW21

vacuum switch 9016G - adjustable scale - 2 thresholds - Set 0 to 23.8 InHg



Product availability: Stock - Normally stocked in distribution facility

Price*: 290.00 USD



Main

Commercial Status	Commercialised
Range of product	9016G
Product or component type	Electromechanical vacuum switch type
Device application	Sensitive control application
Device short name	9016G
Electrical circuit type	Control circuit

Complementary

Factory modification	-
Vacuum switch type of operation	Regulation between two thresholds
Scale type	Adjustable
Value of setting	-
Vacuum sensor size	28.3 inHg
Range on decreasing vacuum	0...28.3 inHg
Approx differential at minimum range	1...9 inHg
Approx differential at mid range	1.7...7.4 inHg
Maximum pressure	100 psi
Maximum permissible pressure - per cycle	100 psi
Local display	Without
Fluid connection type	0.25 inch 18 NPTF UL 508
Electrical connection	Screw-clamp terminals 22...12 AWG
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	8 screw terminals
Pressure actuator	Diaphragm nitrile (Buna-N)
Controlled fluid	Gas -40...250 °F Hydraulic oil -40...250 °F Water -40...250 °F Air -40...250 °F
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N) 3M Scotch-Grip 847 rubber and gasket adhesive
Enclosure material	Die cast aluminum alloy 380
Operating position	Any position
Operating rate	<= 120 cyc/mn -10...185 °F
Repeat accuracy	0.4 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

[In] rated current	0.11 A 250 V DC R300 NEMA rating designation 0.22 A 125 V DC R300 NEMA rating designation 6 A 120 V AC A600 NEMA rating designation 3 A 240 V AC A600 NEMA rating designation
Local signalling	Without
Contacts type and composition	2(NC-NO) DPDT Form ZZ snap action silver nickel contacts
Short circuit protection	10 A cartridge overload and short-circuit protection gL
Mechanical durability	5000000 cycles
Setting	Internal
Product weight	4.6 lb(US)
Height	6.45 in
Depth	4.56 in
Width	4.56 in

Environment

Standards	UL 508
Product certifications	UL listed file E12158 CCN NKPZ and CCN NTHT CSA file LR25490
Protective treatment	None
Ambient air temperature for operation	10...185 °F
Ambient air temperature for storage	10...185 °F
Vibration resistance	2 gn IEC 68-2-6 40...150 Hz
Shock resistance	50 gn IEC 58-2-27
NEMA degree of protection	NEMA 4/4X/13 UL 698

Ordering and shipping details

Category	21541 - 9016 COMMERCIAL VACUUM SWITCH
Discount Schedule	CP7G
GTIN	00785901522904
Nbr. of units in pkg.	1
Package weight(Lbs)	4.56
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 1150 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual

Contractual warranty

Period	18 months
--------	-----------