

Product data sheet

Characteristics

QO2L30S

LOAD CENTER QO MLO 240V 30A 1PH 2SP

Product availability: Stock - Normally stocked in distribution facility

Price*: 41.70 USD



Main

Commercial Status	Commercialised
Product or component type	Load Centre
Range of product	QO
Load centre type	Fixed Mains (lugs)
Line Rated Current	30 A
Number of spaces	2
Short-circuit current	10 kA
Number of circuits	2
Number of tandem circuit breakers	0
Phase	1 phase
System Voltage	120/240 V AC

Complementary

AWG gauge	AWG 14...AWG 4 (copper) AWG 12...AWG 3 (aluminium)
NEMA degree of protection	NEMA 1 indoor
Cover type	Surface cover
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated aluminium busbar
Product certifications	UL listed

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785071
Nbr. of units in pkg.	1
Package weight(Lbs)	2.11
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------