

Product data sheet

Characteristics

QO24L70S

LOAD CENTER QO MLO 240V 70A 1PH 2SP



Product availability: Stock - Normally stocked in distribution facility

Price*: 69.00 USD



Main

Commercial Status	Commercialised
Product or component type	Load Centre
Range of product	QO
Load centre type	Fixed Mains (lugs)
Line Rated Current	70 A
Number of spaces	2
Short-circuit current	10 kA
Number of circuits	4
Number of tandem circuit breakers	2
Phase	1 phase
System Voltage	120/240 V AC

Complementary

AWG gauge	AWG 14...AWG 4 (copper) AWG 12...AWG 3 (aluminium)
NEMA degree of protection	NEMA 1 indoor
Cover type	Surface cover
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated aluminium busbar
Product certifications	UL listed

Ordering and shipping details

Category	00101 - QO 1PH LC,2-8CKT,NEMA 1,3R
Discount Schedule	DE3A
GTIN	00785901785149
Nbr. of units in pkg.	1
Package weight(Lbs)	3.73
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1423 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------