



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 13

3888 ELECTRICALLY CONDUCTIVE RE

SDS No. : 170699
V004.2

Revision: 31.05.2015

printing date: 31.10.2015

Replaces version from: 20.02.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

3888 ELECTRICALLY CONDUCTIVE RE

Contains:

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700)
2,3-epoxypropyl o-tolyl ether
Trimethylolpropane triglycidyl ether
p-tert-Butylphenyl 1-(2,3-epoxy)propyl ether

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Part A of 2-K-Epoxy Adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000
Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Germ cell mutagenicity	Category 2
H341 Suspected of causing genetic defects.	
Chronic hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Warning

Hazard statement:

H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H341 Suspected of causing genetic defects.
H412 Harmful to aquatic life with long lasting effects.

**Precautionary statement:
Prevention**

P273 Avoid release to the environment.
P280 Wear protective gloves/protective clothing.

**Precautionary statement:
Response**

P302+P352 IF ON SKIN: Wash with plenty of water.
P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Conductive epoxy resin

Base substances of preparation:

resins

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Silver 7440-22-4	231-131-3	>= 70- < 90 %	
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	500-033-5 500-033-5 01-2119456619-26	>= 10- < 20 %	Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 Aquatic Chronic 2 H411
2,3-epoxypropyl o-tolyl ether 2210-79-9	218-645-3	>= 1- < 5 %	Muta. 2 H341 Skin Irrit. 2 H315 Aquatic Chronic 2 H411 Skin Sens. 1 H317
Trimethylolpropane triglycidyl ether 30499-70-8		>= 1- < 2,5 %	Skin Irrit. 2; Dermal H315 Skin Sens. 1; Dermal H317 Eye Irrit. 2 H319 Aquatic Chronic 3 H412
p-tert-Butylphenyl 1-(2,3-epoxy)propyl ether 3101-60-8	221-453-2	>= 1- < 2,5 %	Skin Irrit. 2; Dermal H315 Skin Sens. 1; Dermal H317 Eye Irrit. 2 H319 Aquatic Chronic 2 H411

**For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.**

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

EYE: Irritation, conjunctivitis.

SKIN: Redness, inflammation.

SKIN: Rash, Urticaria.

Prolonged or repeated skin contact with silver and its salts may cause a blue-gray discoloration of the skin and mucous membranes that is irreversible (Argyria).

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

5.2. Special hazards arising from the substance or mixture

Formation of toxic gases is possible during heating or in fires.
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

Cool endangered containers with water spray jet.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Wash spillage site thoroughly with soap and water or detergent solution.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.
Avoid skin and eye contact.
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.
Ensure that workrooms are adequately ventilated.
See advice in section 8

Hygiene measures:

Do not eat, drink or smoke while working.
Wash hands before work breaks and after finishing work.
Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

7.3. Specific end use(s)

Part A of 2-K-Epoxy Adhesive

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Silver 7440-22-4 [SILVER (METALLIC)]		0,1	Time Weighted Average (TWA):		EH40 WEL
Silver 7440-22-4 [SILVER, METALLIC]		0,1	Time Weighted Average (TWA):	Indicative	ECLTV

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (freshwater)					0,006 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (marine water)					0,0006 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (intermittent releases)					0,018 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	STP					10 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (freshwater)				0,996 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (marine water)				0,0996 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	soil				0,196 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	oral					11 mg/kg food	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Dermal	Acute/short term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Acute/short term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Dermal	Long term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Workers	Inhalation	Long term exposure - systemic effects		12,25 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Acute/short term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Long term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Inhalation	Acute/short term exposure - systemic effects		0,75 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Inhalation	Long term exposure - systemic effects		0,75 mg/m3	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Acute/short term exposure - systemic effects		0,75 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Long term exposure - systemic effects		0,75 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Avoid eye contact.

Tightly fitting safety goggles

Skin protection:

Suitable protective clothing

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste silver
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	Not applicable
Initial boiling point	> 149,0 °C (> 300,2 °F)
Flash point	> 93,0 °C (> 199,4 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Insoluble
(20 °C (68 °F); Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reaction with strong acids.

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

In case of fire toxic gases can be released.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Inhalative toxicity:

May cause irritation to respiratory system.

Dermal toxicity:

Prolonged or repeated skin contact with silver and its salts may cause a blue-gray discoloration of the skin and mucous membranes that is irreversible (Argyria).

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.

Sensitizing:

May cause an allergic skin reaction.

Mutagenicity:

Suspected of causing genetic defects

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LD50	> 2.000 mg/kg	oral		rat	
2,3-epoxypropyl o-tolyl ether 2210-79-9	LD50	> 2.000 mg/kg	oral		rat	
Trimethylolpropane triglycidyl ether 30499-70-8	LD50	> 2.000 mg/kg	oral			
p-tert-Butylphenyl 1-(2,3- epoxy)propyl ether 3101-60-8	LD50	> 10.000 mg/kg	oral		rat	

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LD50	23.000 mg/kg	dermal		rabbit	
2,3-epoxypropyl o-tolyl ether 2210-79-9	LD50	> 2.000 mg/kg	dermal		rat	
Trimethylolpropane triglycidyl ether 30499-70-8	LD50	> 2.000 mg/kg	dermal		rat	
p-tert-Butylphenyl 1-(2,3- epoxy)propyl ether 3101-60-8	LD50	> 46.400 mg/kg	dermal		rat	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Silver 7440-22-4	slightly irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	slightly irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Silver 7440-22-4	slightly irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 472 (Genetic Toxicology: Escherichia coli, Reverse Mutation Assay)

SECTION 12: Ecological information

General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity

Ecotoxicity:

Harmful to aquatic life with long lasting effects.

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LC50	1,750000 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
	LC50	1,75 mg/l	Fish	96 h	Oncorhynchus mykiss (reported as Salmo gairdneri)	OECD Guideline 203 (Fish, Acute Toxicity Test)
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	NOEC	2,4 mg/l	Algae	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
	EC50	9,4 mg/l	Algae	72 h	Scenedesmus capricornutum	OECD Guideline 201 (Alga, Growth Inhibition Test)
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	NOEC	0,3 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
2,3-epoxypropyl o-tolyl ether 2210-79-9	LC50	7,5 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
2,3-epoxypropyl o-tolyl ether 2210-79-9	EC50	3,3 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

12.2. Persistence and degradability

Persistence and Biodegradability:

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6		aerobic	5 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
2,3-epoxypropyl o-tolyl ether 2210-79-9		aerobic	11 - 17 %	OECD 301 A - F

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

Cured adhesives are immobile.

Bioaccumulative potential:

No data available for the product.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
p-tert-Butylphenyl 1-(2,3-epoxy)propyl ether 3101-60-8	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packaging group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3,00 %
(1999/13/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H341 Suspected of causing genetic defects.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Label elements (DPD):

Xn - Harmful



Risk phrases:

- R36/38 Irritating to eyes and skin.
- R68 Possible risk of irreversible effects.
- R43 May cause sensitisation by skin contact.
- R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

- S23 Do not breathe vapour.
- S24 Avoid contact with skin.
- S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- S37 Wear suitable gloves.
- S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

Contains epoxy constituents. See information supplied by the manufacturer.

Contains:

- Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700),
- 2,3-epoxypropyl o-tolyl ether,
- Trimethylolpropane triglycidyl ether,
- p-tert-Butylphenyl 1-(2,3-epoxy)propyl ether

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.

