



Revision Number: 004.0

Issue date: 10/29/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE 3875 PTB known as 30 CC 3875 EFD PART B	IDH number:	892666
Product type:	Anaerobic Adhesive	Item number:	TC3875B-V19
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Electronic Materials LLC	Telephone: +1 (888) 943-6535		
14000 Jamboree Road	MEDICAL EMERGENCY Phone: Poison Control Center		
Irvine, CA 92606	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkel.com/electronics		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear eye and face protection. Wear protective gloves.
Response:	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage:	Not prescribed
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

6 % of the mixture consists of ingredient(s) of unknown acute toxicity.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Aluminum oxide, fibrous	1344-28-1	30 - 60
Hydroxyalkyl methacrylate	27813-02-1	10 - 30
Polyurethane Methacrylate Resin	Unknown	5 - 10
Methacryloyloxyethyl Ester	Proprietary	5 - 10
High boiling methacrylate	Proprietary	1 - 5
Acrylic acid	79-10-7	1 - 5
Polyglycol dimethacrylate	Proprietary	0.1 - 1
2-Hydroxyethyl methacrylate	868-77-9	0.1 - 1
Substituted Silane	Proprietary	0.1 - 1
Cobalt octoate	136-52-7	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon, oxides of nitrogen, irritating organic vapors. Oxides of boron.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Avoid dust formation. Do not taste or swallow. Keep container closed. Refer to Section 8.
- Storage:** For safe storage, store at or below 10.0 °C (50°F)
Keep in a cool, well ventilated area away from heat, sparks and open flame.
Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Aluminum oxide, fibrous	1 mg/m3 TWA Respirable fraction.	5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust.	None	None
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Polyurethane Methacrylate Resin	None	None	None	None
Methacryloyloxyethyl Ester	None	None	None	None
High boiling methacrylate	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Polyglycol dimethacrylate	None	None	None	None
2-Hydroxyethyl methacrylate	None	None	None	3 ppm Ceiling
Substituted Silane	None	None	None	None
Cobalt octoate	0.02 mg/m3 TWA (as Co)	None	None	None

- Engineering controls:** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
- Respiratory protection:** Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Liquid, Paste
Color: Light, Blue
Odor: Mild
Odor threshold: Not available.
pH: Not available.
Vapor pressure: Not available.
Boiling point/range: Not available.
Melting point/ range: Not available.
Specific gravity: 1.69
Vapor density: Not available.
Flash point: 107 °C (224.6 °F)

Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0.05 %; 0.90 g/l EPA Method 24
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Irritating organic vapours. Oxides of boron.
Incompatible materials:	Oxidizing agents. Reducing agents. Acids. Bases. Heat, sunlight, or UV light. Heavy metals.
Reactivity:	Not available.
Conditions to avoid:	Heat, flames, sparks and other sources of ignition. Store away from incompatible materials. Ultraviolet radiation. Extremes of temperature and direct sunlight.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact: Causes skin irritation. May cause allergic skin reaction.
Eye contact: Causes serious eye irritation.
Ingestion: Ingestion can cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Aluminum oxide, fibrous	None	Irritant, Nuisance dust, Corrosive
Hydroxyalkyl methacrylate	None	Irritant, Allergen
Polyurethane Methacrylate Resin	None	Irritant, Allergen
Methacryloyloxyethyl Ester	None	No Records
High boiling methacrylate	None	Irritant, Allergen
Acrylic acid	Oral LD50 (RAT) = 33.5 mg/kg Oral LD50 (RAT) = 2.5 g/kg Oral LD50 (RAT) = 193 mg/kg Oral LD50 (RAT) = 1,250 mg/kg Inhalation LC50 (RAT, 4 h) = 1,200 mg/l	Allergen, Corrosive, Irritant, Kidney, Liver
Polyglycol dimethacrylate	None	Irritant, Allergen
2-Hydroxyethyl methacrylate	Oral LD50 (RAT) = 11.2 g/kg Oral LD50 (RAT) = 5,050 mg/kg	Irritant, Allergen
Substituted Silane	None	Irritant, Allergen
Cobalt octoate	None	Allergen, Blood, Ear, Irritant, Kidney, Lung, Nervous System, Respiratory, Thyroid, Vascular

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Aluminum oxide, fibrous	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Polyurethane Methacrylate Resin	No	No	No
Methacryloyloxyethyl Ester	No	No	No
High boiling methacrylate	No	No	No
Acrylic acid	No	No	No
Polyglycol dimethacrylate	No	No	No
2-Hydroxyethyl methacrylate	No	No	No
Substituted Silane	No	No	No
Cobalt octoate	No	Group 2B	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health

CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Aluminum oxide, fibrous (CAS# 1344-28-1). Acrylic acid (CAS# 79-10-7). Cobalt octoate (CAS# 136-52-7). Fatty acids, tall-oil, cobalt salts (CAS# 61789-52-4).

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 10/29/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.