

Hi-Spot 50

HS50 240V 40W 25° E14 SV1

0021084



Range Features

- Retrofit solution for E14 incandescent R50 lamps
- Halogen light without the need for a transformer
- Unique, patented spiral reflector design for uniform beam pattern
- 100% dimmable
- For use in mains voltage E14 cap downlights, spotlights and luminaires
- Average rated life 2000 hrs



PRODUCT OVERVIEW

Lamp finish	Aluminium
Lamp shape	Reflector
Colour temperature (K)	2700
CRI (Ra)	100
Dimmable	Yes
EAN code	5410288210841
Energy class	D
Cap/Base	E14
Beam angle(°)	25
Type	PAR 16
Watt (Nominal) (W)	40
Light colour	827 Homelight
Ordering number	0021084
Average life (Rated) (h)	2000
Luminous flux (Rated) (lm)	265
Technology	Halogen
Voltage (V)	240

DATA TABLE

General data

Average life (Nominal) (h)	2000
Control gear required	No
Lamp finish	Aluminium
Lamp shape	Reflector
Dimmable	Yes
EAN code	5410288210841
Energy class	D
Energy saving lamp	No

Hi-Spot 50

HS50 240V 40W 25° E14 SV1

0021084

Fixture rating	Open
General application	Residential & Consumer;Hospitality;
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-3
IEC Reference 3	IEC 60630
Intended purpose	General lighting
Cap/Base	E14
Lamp mercury content (mg)	0
Type	PAR 16
No. of switching cycles before premature failure (min)	> 8000
Ordering number	0021084
Range features	Retrofit solution for E14 incandescent R50 lamps Halogen light without the need for a transformer Unique, patented spiral reflector design for uniform beam pattern 100% dimmable For use in mains voltage E14 cap downlights, spotlights and luminaires Average rated life 2000 hrs
Product name	HS50 240V 40W 25° E14 SV1
Average life (Rated) (h)	2000
Special purpose lamp	No
Starting time (max) (s)	0
Technology	Halogen
Transformer required	No
Sales pack quantity	15
Warm-up time to 60% of full light (max) (s)	Instant Full Light
E-number SE	8355900
E-number FI	4749302

Optical data

Colour temperature (K)	2700
CRI (Ra)	100
Beam angle(°)	25
Light colour	827 Homelight
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	265
Peak intensity (cd)	950
Luminous flux (Rated) (lm)	265
Suitable for accent lighting	Yes
Beam angle (Rated) (°)	25

Hi-Spot 50

HS50 240V 40W 25° E14 SV1

0021084


Electrical data

Current (A)	0.17
kWh per 1000 hours burning time	40
Lamp power factor	1
Watt (Nominal) (W)	40
Watt (Rated) (W)	40
Voltage (V)	240

Physical data

Max. Lamp Diameter (mm) - D	50
Lamp Length (mm) - C/L	77
Single packaging type	Box/Sleeve
Weight (kg)	0.06
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Outer package dimensions (L x W x H) (cm)	28.00 x 17.00 x 9.50
Single package dimensions (L x W x H) (cm)	4.80 x 4.80 x 8.00

TECHNICAL DRAWINGS



Hi-Spot 50

HS50 240V 40W 25° E14 SV1

0021084

