

GA352QR7GF471KW01#

“ # ” indicates a package specification code.

Recommended

In Production

General

Safety standard

125℃


Reflow OK


RoHS

REACH

< List of part numbers with package codes >  
GA352QR7GF471KW01L , GA352QR7GF471KW01K

Shape





L size	5.7 ± 0.4mm
W size	2.8 ± 0.3mm
T size	1.5 +0.0/-0.3mm
External terminal width e	0.3mm min.
Distance between external terminals g	4.0mm min.
Size code in inch(mm)	2211 (5728)

Notes

X1/Y2 Class Certified Products
--------------------------------

References

Packaging	Specifications	Minimum quantity
L	180mm Embossed taping	1000
K	330mm Embossed taping	4000

Mass (typ.)	
1 piece	120mg


Specifications

Capacitance	470pF ± 10%
Rated voltage	250Vac
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 125
Operating temperature range	-55 to 125


⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


Frequency characteristics (ESR, Impedance)




S parameter (Smith chart S11)




DC bias characteristics



AC voltage characteristics



Capacitance - temperature characteristics



This PDF data has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.