

## NCP21XV103J03RA












#### Appearance & Shape









#### **Features**

- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-constant
- 4. Flow / Reflow soldering possible
- 5. Same B-

Constant in the same resistance in the three sizes (0805 size / 0603 s

Easy to use smaller size in the circuits

- 6. Lead is not contained in the product.
- 7. NCP series are recognized by UL/cUL (UL1434, File No.E137188).



### Applications

Other Usage

1. Temperature compensation for transistor, IC and crystal os



#### Packaging Information

| Packaging | Specifications      | Minimum<br>Order Quantity |
|-----------|---------------------|---------------------------|
| RA        | 180mm Embossed Tape | 4000                      |

1 of 3

#### Attention

Authin Malasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

URL : http://www.murata.com/



Last updated :2015/12/04



# NCP21XV103J03RA

# Specifications

| Resistance (25°C)                       | 10kΩ           |
|---|----------------|
| Resistance Value Tolerance (at 25°C)    | ±5%            |
| B-Constant (25/50°C)                    | 3900K          |
| B-Constant (25/50°C) Tolerance          | ±3%            |
| B-Constant (25/80°C) (Reference Value)  | 3930K          |
| B-Constant (25/85°C) (Reference Value)  | 3934K          |
| B-Constant (25/100°C) (Reference Value) | 3944K          |
| Permissive Operating Current (25°C)     | 0.44mA         |
| Rated Electric Power (25°C)             | 200mW          |
| Typical Dissipation Constant (25°C)     | 2mW/°C         |
| Operating Temperature Range             | -40°C to 125°C |
| Shape                                   | SMD            |

#### 2 of 3

ATTENTION

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed space.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




URL : http://www.murata.com/

Last updated : 2015/12/04



#### NCP21XV103J03RA





Resistance-Temperature Characteristics

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



URL: http://www.murata.com/

Last updated : 2015/12/04