

Small Signal Schottky Diode



MECHANICAL DATA

Case: DO-35

Weight: approx. 125 mg

Cathode band color: Black

Packaging codes/options:

TR/10K per 13" reel (52 mm tape), 50K/box

TAP/10K per ammpack (52 mm tape), 50K/box

FEATURES

- For general purpose applications
- This diode features very low turn-on voltage and fast switching. This device is protected by a PN junction guard ring against excessive voltage, such as electrostatic discharges
- This diode is also available in the SOD-123 case with type designation BAT46W-V and in the MiniMELF case with type designations LL46
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

| PARTS TABLE | | | | |
|-------------|-----------------------|-----------------------|--------------|-----------------------|
| PART | ORDERING CODE | INTERNAL CONSTRUCTION | TYPE MARKING | REMARKS |
| BAT46 | BAT46-TR or BAT46-TAP | Single diode | BAT46 | Tape and reel/ammpack |

| ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified) | | | | | |
|---|--|-----------|-------|------|--|
| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT | |
| Repetitive peak reverse voltage | | V_{RRM} | 100 | V | |
| Forward continuous current ⁽¹⁾ | | I_F | 150 | mA | |
| Repetitive peak forward current ⁽¹⁾ | $t_p < 1\text{ s}, \delta < 0.5$ | I_{FRM} | 350 | mA | |
| Surge forward current ⁽¹⁾ | $t_p < 10\text{ ms}$ | I_{FSM} | 750 | mA | |
| Power dissipation ⁽¹⁾ | $T_{amb} = 80\text{ }^{\circ}\text{C}$ | P_{tot} | 150 | mW | |

Note

⁽¹⁾ Valid provided that electrodes are kept at ambient temperature

| THERMAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified) | | | | | |
|--|--|------------|---------------|--------------------|--|
| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT | |
| Thermal resistance junction to ambient air | Valid provided that electrodes are kept at ambient temperature | R_{thJA} | 300 | K/W | |
| Junction temperature | | T_j | 125 | $^{\circ}\text{C}$ | |
| Ambient operating temperature range | | T_{amb} | - 65 to + 125 | $^{\circ}\text{C}$ | |
| Storage temperature range | | T_{stg} | - 65 to + 150 | $^{\circ}\text{C}$ | |

| ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified) | | | | | | |
|--|--|------------|------|------|------|---------------|
| PARAMETER | TEST CONDITION | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| Reverse breakdown voltage | $I_R = 100\text{ }\mu\text{A}$ (pulsed) | $V_{(BR)}$ | 100 | | | V |
| Leakage current ⁽¹⁾ | $V_R = 1.5\text{ V}$ | I_R | | | 0.5 | μA |
| | $V_R = 1.5\text{ V}, T_j = 60\text{ }^{\circ}\text{C}$ | I_R | | | 5 | μA |
| | $V_R = 10\text{ V}$ | I_R | | | 0.8 | μA |
| | $V_R = 10\text{ V}, T_j = 60\text{ }^{\circ}\text{C}$ | I_R | | | 7.5 | μA |
| | $V_R = 50\text{ V}$ | I_R | | | 2 | μA |
| | $V_R = 50\text{ V}, T_j = 60\text{ }^{\circ}\text{C}$ | I_R | | | 15 | μA |
| | $V_R = 75\text{ V}$ | I_R | | | 5 | μA |
| Forward voltage ⁽¹⁾ | $I_F = 0.1\text{ mA}$ | V_F | | | 250 | mV |
| | $I_F = 10\text{ mA}$ | V_F | | | 450 | mV |
| | $I_F = 250\text{ mA}$ | V_F | | | 1000 | mV |
| Diode capacitance | $V_R = 0\text{ V}, f = 1\text{ MHz}$ | C_D | | 10 | | pF |
| | $V_R = 1\text{ V}, f = 1\text{ MHz}$ | C_D | | 6 | | pF |


Note
⁽¹⁾ Pulse test; $t_p \leq 300\text{ }\mu\text{s}$, $\delta < 2\%$
TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Typical Instantaneous Forward Characteristics




Fig. 3 - Admissible Power Dissipation vs. Ambient Temperature





Fig. 2 - Typical Reverse Characteristics

PACKAGE DIMENSIONS in millimeters (inches): **DO-35**



Rev. 6 - Date: 19. December 2011
 Document no.: SB-V-3906.04-031(4)
 94 9366



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.