


Datasheet

Art.No. 55.503.1053.0

Feed-through terminal WKM 2,5/ 15 /V0

Feed-through DIN rail terminal block with screw connection for mounting on TS 15, nominal cross section 2.5 mm², width 5 mm, color g ray



Approvals



Technical data

General

Nominal cross section	2.5 mm ²
Colour	Grey
Number of levels	1
Number of clamp positions per level	2
Width/grid dimension	5 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Explosion-tested version "Ex e"	Yes
Mounting method	DIN rail (top hat rail) 15 mm
Terminal blocks for electrical installations	Yes

Technical data

Rated current	25 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Closing plate required	Yes
Type of insulation material	Thermoplastic
Length	32 mm

Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	0.5 mm ²
Maximum cross section solid	4 mm ²
Minimum cross section fine stranded	0.5 mm ²

Maximum cross section fine stranded	2.5 mm ²
Wire strip length	9 mm
Torque conductor mounting	0.4 Nm

Technical Data UL/CSA

Cross section UL	22-14 AWG
Voltage UL	300 V
Current factory wiring	10 A
Current field wiring	10 A
Cross section CSA	22-12 AWG
Voltage CSA	600 V
Current CSA	25 A

Classification

ECLASS 8.1	27141120: Feed-through terminal block
ETIM 5.0	EC000897: Feed-through terminal block
ETIM 4.0	EC000897: Feed-through terminal block
ETIM 3.0	EC000897: Feed-through terminal block