

# **C3D20060D**Silicon Carbide Schottky Diode

# Z-REC™ RECTIFIER

 $V_{RRM} = 600 \text{ V}$   $I_{F}(T_{c}=135^{\circ}C) = 28 \text{ A}^{**}$   $Q_{c} = 50 \text{ nC}^{**}$ 

#### **Features**

- 600-Volt Schottky Rectifier
- Zero Reverse Recovery Current
- Zero Forward Recovery Voltage
- High-Frequency Operation
- Temperature-Independent Switching Behavior
- Extremely Fast Switching
- Positive Temperature Coefficient on V<sub>F</sub>

#### **Benefits**

- Replace Bipolar with Unipolar Rectifiers
- Essentially No Switching Losses
- Higher Efficiency
- Reduction of Heat Sink Requirements
- Parallel Devices Without Thermal Runaway

# PIN 2O O CASE PIN 3O

# **Applications**

- Switch Mode Power Supplies
- Power Factor Correction
  - Typical PFC P<sub>out</sub>: 2000W-4000W
- Motor Drives
  - Typical Power : 5HP-10HP



**Package** 

TO-247-3

Part Number	Package	Marking
C3D20060D	TO-247-3	C3D20060

Halogen-Free

# **Maximum Ratings** (T<sub>c</sub> = 25 °C unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
V <sub>RRM</sub>	Repetitive Peak Reverse Voltage	600	V		
$V_{RSM}$	Surge Peak Reverse Voltage	600	V		
V <sub>DC</sub>	DC Blocking Voltage	600	V		
I <sub>F</sub>	Continuous Forward Current (Per Leg/Device)	29.5/59 14/28 10/20	А	T <sub>c</sub> =25°C T <sub>c</sub> =135°C T <sub>c</sub> =152°C	
$I_{FRM}$	Repetitive Peak Forward Surge Current (Per Leg/Device)	67/134 44/88	А	$T_c$ =25°C, $t_p$ =10 ms, Half Sine Wave, D=0.3 $T_c$ =110°C, $t_p$ =10 ms, Half Sine Wave, D=0.3	
$\boldsymbol{I}_{\text{FSM}}$	Non-Repetitive Peak Forward Surge Current (Per Leg/Device)	90/157 71/115	А	$T_c$ =25°C, $t_p$ =10ms, Half Sine Wave, D=0.3 $T_c$ =110°C, $t_p$ =10 ms, Half Sine Wave, D=0.3	
$\boldsymbol{I}_{\text{FSM}}$	Non-Repetitive Peak Forward Surge Current (Per Leg/Device)	250/500	А	$T_c=25$ °C, $t_p=10$ µs, Pulse	
P <sub>tot</sub>	Power Dissipation (Per Leg)	136.3 59	W	T <sub>c</sub> =25°C T <sub>c</sub> =125°C	
$T_{\scriptscriptstyle \mathrm{J}}$ , $T_{\scriptscriptstyle \mathrm{stg}}$	Operating Junction and Storage Temperature	-55 to +175	°C		
	TO-247 Mounting Torque	1 8.8	Nm lbf-in	M3 Screw 6-32 Screw	

<sup>\*</sup> Per Leg, \*\* Per Device



#### **Electrical Characteristics (Per Leg)**

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
V <sub>F</sub>	Forward Voltage	1.5 2.0	1.8 2.4	V	$I_F = 10 \text{ A } T_J = 25^{\circ}\text{C}$ $I_F = 10 \text{ A } T_J = 175^{\circ}\text{C}$	
I <sub>R</sub>	Reverse Current	10 20	50 200	μΑ	$V_R = 600 \text{ V } T_J = 25^{\circ}\text{C}$ $V_R = 600 \text{ V } T_J = 175^{\circ}\text{C}$	
Q <sub>c</sub>	Total Capacitive Charge	25		nC	$V_R = 600 \text{ V, } I_F = 10 \text{ A}$ $di/dt = 500 \text{ A/}\mu\text{s}$ $T_J = 25^{\circ}\text{C}$	
С	Total Capacitance	480 50 42		pF	$V_R = 0 \text{ V, } T_J = 25^{\circ}\text{C, } f = 1 \text{ MHz}$ $V_R = 200 \text{ V, } T_J = 25^{\circ}\text{C, } f = 1 \text{ MHz}$ $V_R = 400 \text{ V, } T_J = 25^{\circ}\text{C, } f = 1 \text{ MHz}$	

#### Note:

#### **Thermal Characteristics**

Symbol	Parameter	Тур.	Unit
$R_{\theta JC}$	Thermal Resistance from Junction to Case	1.1** 0.55*	°C/W

<sup>\*\*</sup> Per Leg, \* Both Legs

#### **Typical Performance (Per Leg)**




Figure 1. Forward Characteristics





Figure 2. Reverse Characteristics

<sup>1.</sup> This is a majority carrier diode, so there is no reverse recovery charge.



# **Typical Performance (Per Leg)**






Figure 3. Current Derating

Figure 4. Capacitance vs. Reverse Voltage




Figure 5. Transient Thermal Impedance



#### **Typical Performance (Per Leg)**




Figure 6. Power Derating

# **Diode Model (Per Leg)**

$$\begin{array}{c|c} - & & \\ \hline V_T & R_T \end{array}$$


$$Vf_T = V_T + If^*R_T$$
 
$$V_T = 0.98 + (T_J^* - 1.6^*10^{-3})$$
 
$$R_T = 0.04 + (T_J^* 0.522^*10^{-3})$$


Note:  $T_i$  = Diode Junction Temperature In Degrees Celsius



### **Package Dimensions**


Package TO-247-3





	Inc	hes	Millimeters		
POS	Min Max		Min	Max	
Α	.605	.635	15.367	16.130	
В	.800	.831	20.320	21.10	
С	.780	.800	19.810	20.320	
D	.095	.133	2.413	3.380	
Е	.046	.052	1.168	1.321	
F	.060	.095	1.524	2.410	
G	.215	.215 TYP 5.460 TYP		) TYP	
Н	.175	.205	4.450	5.210	
J	.075	.085	1.910	2.160	
K	6°	21°	6°	21°	
L	4°	6°	4°	6°	
М	2°	4°	2°	4°	
N	2°	4°	2°	4°	
Р	.090	.100	2.286	2.540	
Q	.020	.030	.508	.762	
R	9°	11°	9°	11°	
S	9°	11°	9°	11°	
Т	2°	8°	2°	8°	
U	2°	8°	2°	8°	
V	.137	.144	3.487	3.658	
W	.210	.248	5.334	6.300	
Х	.502	.557	12.751	14.150	
Υ	.637	.695	16.180	17.653	
Z	.038	.052	0.964	1.321	
AA	.110	.140	2.794	3.556	
ВВ	.030	.046	0.766	1.168	
CC	.161	.176	4.100	4.472	

## **Recommended Solder Pad Layout**



Part Number	Package	Marking	
C3D20060D	TO-247-3	C3D20060	

Note: Recommended soldering profiles can be found in the applications note here:  $\label{lem:htp://www.cree.com/~/media/Files/Cree/Power/Application%20Notes/CPWRAN04A.pdf} \label{lem:htp://www.cree.com/~/media/Files/Cree/Power/Application%20Notes/CPWRAN04A.pdf}$ 





#### **Notes**

#### RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Cree representative or from the Product Documentation sections of www.cree.com.

#### REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact a Cree representative to insure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

• This product has not been designed or tested for use in, and is not intended for use in, applications implanted into the human body nor in applications in which failure of the product could lead to death, personal injury or property damage, including but not limited to equipment used in the operation of nuclear facilities, life-support machines, cardiac defibrillators or similar emergency medical equipment, aircraft navigation or communication or control systems, air traffic control systems, or weapons systems.