



Revision Number: 005.0

Issue date: 07/31/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE AA 330 1K GEN.BOND ACRYLIC known as Loctite 330	IDH number:	193975
Product type:	Acrylic Adhesive	Item number:	33041
Restriction of Use:	None identified	Region:	United States
Company address:	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information:	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: COMBUSTIBLE LIQUID.
CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE DAMAGE.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	4
SKIN IRRITATION	2
SERIOUS EYE DAMAGE	1
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
Storage:	Store in a well-ventilated place. Keep cool.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Tetrahydrofurfuryl methacrylate	2455-24-5	30 - 60
Methacrylic acid	79-41-4	5 - 10
Alkyl methacrylate	Proprietary	5 - 10
Epoxy resin	Proprietary	1 - 5
Methacrylate monomer	Proprietary	1 - 5
Talc	14807-96-6	0.1 - 1
Cumene hydroperoxide	80-15-9	0.1 - 1
1,1,2-Trichloroethane	79-00-5	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers. In case of fire, keep containers cool with water spray.
Hazardous combustion products:	Oxides of carbon. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling: Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Refer to Section 8.

Storage: For safe storage, store at or below 38 °C (100.4 °F)
Keep in a cool, well ventilated area away from heat, sparks and open flame.
Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Tetrahydrofurfuryl methacrylate	None	None	None	None
Methacrylic acid	20 ppm TWA	None	None	None
Alkyl methacrylate	None	None	None	None
Epoxy resin	None	None	None	None
Methacrylate monomer	None	None	None	None
Talc	2 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 2.4 MPPCF TWA Respirable. 0.1 mg/m3 TWA Respirable. 0.3 mg/m3 TWA Total dust.	None	50 ppm
Cumene hydroperoxide	None	None	1 ppm (6 mg/m3) TWA (SKIN)	None
1,1,2-Trichloroethane	10 ppm TWA (SKIN)	10 ppm (45 mg/m3) PEL (SKIN)	None	None

Engineering controls: Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection: Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection: Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection: Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene, Butyl-rubber, or nitrile-rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Liquid
Color: Amber
Odor: Sharp, Irritating
Odor threshold: Not available.
pH: Not available.
Vapor pressure: < 10 mm hg (26.7 °C (80.1 °F))
Boiling point/range: > 148.9 °C (> 300°F)
Melting point/ range: Not available.
Specific gravity: 1.16
Vapor density: Not available.
Flash point: 83 °C (181.4 °F) Tagliabue closed cup

Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available.
VOC content:	1.59 %; 18.4 g/l
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials.
Hazardous decomposition products:	Oxides of carbon. Oxides of sulfur. Toxic chlorides. Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents. Strong reducing agents. Strong acids. Alkalis. Free radical initiators. Oxygen scavengers.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials. Extremes of temperature and direct sunlight. UV light. Freezing conditions.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system. May cause irritation to nose and throat.

Skin contact: Causes skin irritation. May cause allergic skin reaction.

Eye contact: Causes serious eye damage.

Ingestion: May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Tetrahydrofurfuryl methacrylate	None	Irritant, Allergen
Methacrylic acid	Oral LD50 (RABBIT) = 1,200 mg/kg Oral LD50 (RAT) = 1,060 mg/kg Oral LD50 (RAT) = 2,224 mg/kg Dermal LD50 (RABBIT) = 500 mg/kg Inhalation LC50 (RAT, 4 h) = 7.1 mg/l	Corrosive, Irritant, Allergen
Alkyl methacrylate	Oral LD50 (RAT) = > 2,000 mg/kg	Irritant, Allergen
Epoxy resin	None	Allergen, Irritant
Methacrylate monomer	None	Irritant, Allergen
Talc	None	Irritant, Lung, Some evidence of carcinogenicity
Cumene hydroperoxide	None	Allergen, Central nervous system, Corrosive, Irritant, Mutagen
1,1,2-Trichloroethane	Oral LD50 (RAT) = 835 mg/kg Oral LD50 (RAT) = 100 - 200 mg/kg Dermal LD50 (RABBIT) = 5,377 mg/kg	Irritant, Central nervous system, Lung, Liver, Kidney, Immune system, Some evidence of carcinogenicity, Mutagen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Tetrahydrofurfuryl methacrylate	No	No	No
Methacrylic acid	No	No	No
Alkyl methacrylate	No	No	No
Epoxy resin	No	No	No
Methacrylate monomer	No	No	No
Talc	No	Group 2B	No
Cumene hydroperoxide	No	No	No
1,1,2-Trichloroethane	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Fire, Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis
CERCLA Reportable quantity: Cumene hydroperoxide (CAS# 80-15-9) 10 lbs. (4.54 kg)
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 07/31/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.