

MicroSmart 4pt Analog Output Module

Features

- 4-pt Analog Output Module
- 0-10V DC, 4-20mA, 12-bit resolution
- Applicable standards: UL508, ANSI/ISA 12.12.01-2007 EN61131-2 2007 CSA 22.2 No, 142 No, 213
- UL listed, CE marking






General Specifications

	FC4A-K4A1
Rated Power Voltage	24V DC
Allowable Voltage Range	20.4 to 28.8V DC
Connector on Mother Board	MC1.5/11-G-3.81BK (Phoenix Contact)
Connector Insertion/Removal Durability	100 times minimum
Internal Current Draw	65mA (5V DC)
internal current braw	0mA (24V DC)
External Current Draw (Note)	130mA (24V DC)
Weight (Approx.)	100g


Note: The external current draw is the value when all analog inputs are used and the analog output value is at 100%.

Dimensions (mm)



Terminal Arrangement & Wiring Diagram

Applicable Terminal Block: FC4A-PMT11P (supplied with module)



	(
	24V DC	Fuse	Terminal No.	Channel
	\vdash		+	
	_ '		-	24V DC
			FG	
Analog voltage/current input device Analog voltage/current input device Analog voltage/current input device Analog voltage/current input device		+	+	оито
	-	-	0010	
	+	+	OUT1	
		1	0011	
	+	+	OUT2	
			-	0012
	Analog voltage/current	+	+	OUT3
	input device		-	0013

- Connect a fuse appropriate for the applied voltage and current draw, as shown in the diagram. This is required when equipment containing the MicroSmart is used in Europe.
- Do not connect any wiring to unused terminals.
- When the analog I/O module may malfunction due to noise, use the shielded cable for the analog input and output and connect both ends of the shield to a ground.

Output Specifications

			FC4A-K4A1	
Output Range		Voltage	0 to 10V DC	
		Current	4 to 20mA	
Load	Load Impedance		1k Ω minimum (voltage), 300Ω maximum (current)	
	Applicable Load Type		Resistive load	
DA Conversion	Settling Time		2ms/ch (Note 1)	
DA CONVENSION	Total Output System Transfer Time		2ms x channels + 1 scan time	
	Maximum Error at 25°C		±0.2% of full scale	
	Temperature Coefficient		±0.15% of full scale/°C	
	Repeatability after Stabilization Time		±0.5% of full scale	
Output Error	Output Voltage Drop		±1% of full scale	
	Non-lineality		±0.2% of full scale	
	Output Ripple		20mV maximum	
	Overshoot		0%	
	Total Error		±1% of full scale	
Data	Digital Resolution		4096 increments (12 bits)	
	Voltage		2.5mV	
	Current		4μΑ	
Output Value	Data Type in Application Program		0 to 4095	
of LSB			Optional: -32768 to 32767 (selectable for each channel) (Note 2)	
	Monotonicity		Yes	
	Current Loop Open		Not detectable	
Noise Resistance	Maximum Temporary Deviation during Electrical Noise Tests (Note 3)		±4% maximum	
	Recommended Cable for Noise Immunity		Twisted pair cable	
	Crosstalk		2 LSB maximum	
Isolation			Between input and power circuit: Transformer isolated	
			Between input and internal circuit: Photocoupler isolated	
Effect of Improper Output Connection			No damage	
Selection of Analog Output Signal Type			Using programming software	
Calibration or Verification to Maintain Rated Accuracy		ed Accuracy	Not available	

Note 1: Rise time is not included.

- Note 2: The data processed in the analog I/O module can be linear-converted to a value between –32768 and 32767.

 The optional range designation, and analog I/O data minimum and maximum values can be selected using data registers allocated to analog I/O modules.
- Note 3: For analog I/O modules of version 200 or higher, the value represents when 1 kV is directly applied to the power supply line and a 1 kV clamp voltage is applied to I/O lines. For analog I/O modules earlier than version 200, the value represents when a 500V clamp voltage is applied to the power supply and I/O lines.