

## Fusible, Non-Flammable Metal Film Ledged Resistors



### DESCRIPTION

A homogeneous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with a gray, flame retardant lacquer which provides electrical, mechanical, and climatic protection. The encapsulant is resistant to all cleaning solvents in accordance with **IEC 60068-2-45**.

### FEATURES

- Technology: metal film
- Overload protection without risk of fire
- Wide range of overload currents (refer Fusing Characteristics graphs)
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS  
COMPLIANT**

### APPLICATIONS


- Audio
- Video

TECHNICAL SPECIFICATIONS		
DESCRIPTION	NFR25	NFR25H
Resistance range <sup>(1)</sup>	0.22 Ω to 15 kΩ	0.22 Ω to 15 kΩ
Resistance tolerance	± 5 %	± 5 %
Resistance series	E24	E24
Rated dissipation $P_{70}$	0.33 W	0.5 W
Thermal resistance ( $R_{th}$ )	240 K/W	150 K/W
Temperature coefficient		
0.22 Ω ≤ R ≤ 4.7 Ω	≤ ± 200 ppm/K	≤ ± 200 ppm/K
4.7 Ω ≤ R ≤ 15 Ω	≤ ± 200 ppm/K	≤ ± 100 ppm/K
15 Ω ≤ R ≤ 15 kΩ	≤ ± 100 ppm/K	≤ ± 100 ppm/K
Operating voltage, $U_{max}$ . DC or RMS	250 V	350 V
Basic specifications	IEC 60 115-1	IEC 60 115-1
Climatic category (IEC 60068-1)	55/155/56	55/155/56
Maximum resistance change for resistance range, ΔR max., after:		
Load (1000 h, $P_{70}$ ):	± (1 % R + 0.05 Ω)	± (1 % R + 0.05 Ω)
Long term damp heat test (56 days):	± (1 % R + 0.05 Ω)	± (1 % R + 0.05 Ω)
Soldering (260 °C, 10 s):	± (0.25 % R + 0.05 Ω)	± (0.25 % R + 0.05 Ω)

### Notes

- R value is measured with probe distance of 24 mm ± 1 mm using 4-terminal method
- <sup>(1)</sup> Ohmic values (other than resistance range) are available on request

PACKAGING					
MODEL	TAPING	AMMOPACK		REEL	
		PIECES	CODE	PIECES	CODE
NFR25, NFR25H	Axial, 52 mm	5000	A5	5000	R5
		1000	A1		
NFR25, NFR25H	Radial	2000	N2	-	-


**DIMENSIONS**


DIMENSIONS (Resistor types, mass, and relevant physical dimensions)					
TYPE	D <sub>max.</sub> (mm)	L <sub>1</sub> max. (mm)	L <sub>2</sub> max. (mm)	Ø d (mm)	MASS (mg)
NFR25	2.5	6.5	7.5	0.58 ± 0.05	201
NFR25H					

PART NUMBER AND PRODUCT DESCRIPTION						
Part Number: NFR250002207JA100						
N	F	R	2	5	0	0
0	0	0	0	2	2	0
7	J	A	1	0	0	
MODEL/SIZE	VARIANT	TCR/MATERIAL	VALUE	TOLERANCE	PACKAGING <sup>(1)</sup>	SPECIAL
NFR2500 NFR25H	0 = neutral Z = value overload (special)	0 = standard	3 digit value 1 digit multiplier MULTIPLIER 7 = *10 <sup>-3</sup> 8 = *10 <sup>-2</sup> 9 = *10 <sup>-1</sup> 0 = *10 <sup>0</sup> 1 = *10 <sup>1</sup> 2 = *10 <sup>2</sup>	J = ± 5 %	N2 A5 A1 R5	Up to 2 digits are used for all special parts. 00 = standard
Product Description: NFR25 5 % A1 R22						
NFR25	5 %	A1	R22			
MODEL / SIZE	TOLERANCE	PACKAGING <sup>(1)</sup>	RESISTANCE VALUE			
NFR25 NFR25H	± 5 %	N2 A5 A1 R5	1K0 = 1 kΩ 4R7 = 4.7 Ω			

**Notes**

- The PART NUMBER is shown to facilitate the introduction of the unified part numbering system
- <sup>(1)</sup> Please refer to table PACKAGING, see next page

**PRODUCTS WITH RADIAL LEADS (NFR25, NFR25H)**


DIMENSIONS (Radial taping)				
SYMBOL	PARAMETER	VALUE	TOLERANCE	UNIT
P	Pitch of components	12.7	± 1.0	mm
P <sub>0</sub>	Feed-hole pitch	12.7	± 0.2	mm
P <sub>1</sub>	Feed-hole centre to lead at topside at the tape	3.85	± 0.5	mm
P <sub>2</sub>	Feed-hole center to body center	6.35	± 1.0	mm
F	Lead-to-lead distance	4.8	+ 0.7 / - 0	mm
W	Tape width	18.0	± 0.5	mm
W <sub>0</sub>	Minimum hold down tape width	5.5	-	mm
H <sub>1</sub>	Component height	29.0	Max.	mm
H <sub>0</sub>	Lead wire clinch height	16.5	± 0.5	mm
H	Height of component from tape center	19.5	± 1	mm
D <sub>0</sub>	Feed-hole diameter	4.0	± 0.2	mm
L	Maximum length of snapped lead	11.0	-	mm
L <sub>1</sub>	Minimum lead wire (tape portion) shortest lead	2.5	-	mm

**Note**

- Please refer document number 28721 "Packaging" for more detail

**MARKING**

The nominal resistance and tolerance are marked on the resistor using four colored bands in accordance with IEC 60062, marking codes for resistors and capacitors. For ease of recognition a fifth ring is added, which is violet for type NFR25 and white for type NFR25H.

**FUNCTIONAL PERFORMANCE, PRODUCT CHARACTERIZATION**

Standard values of nominal resistance are taken from the E24 series for resistors with a tolerance of ± 5 %.

The values of the E24 series are in accordance with IEC 60063.

**OUTLINES**

The length of the body (L<sub>1</sub>) is measured by inserting the leads into holes of two identical gauge plates and moving these plates parallel to each other until the resistor body is clamped without deformation (IEC 60294).

LIMITING VALUES		
TYPE	LIMITING VOLTAGE $U^{(1)}$ (V)	LIMITING POWER $P_{70}$ (W)
NFR25	250	0.33
NFR25H	350	0.5


**Note**

- (1) The maximum voltage that may be continuously applied to the resistor element, see IEC 60115-1. The maximum permissible hot-spot temperature is 155 °C.



### DERATING

The power that the resistor can dissipate depends on the operating temperature.




Maximum dissipation ( $P_{max}$ ) in percentage of rated power as a function of the ambient temperature ( $T_{amb}$ )


### FUSING CHARACTERISTICS

The resistors will fuse without the risk of fire and within an indicated range of overload. Fusing means that the resistive value of the resistor increases at least 100 times.


The fusing characteristic is measured under constant voltage.



**NFR25** This graph is based on measured data which may deviate according to the application.  
Fusing Characteristics:  $\leq 1 \Omega$




**NFR25** This graph is based on measured data which may deviate according to the application.  
Fusing Characteristics:  $1 \Omega \leq R \leq 15 \Omega$




**NFR25** This graph is based on measured data which may deviate according to the application.  
Fusing Characteristics:  $15 \Omega \leq R \leq 15 \text{ k}\Omega$



### FUSING CHARACTERISTICS




**NFR25** This graph is based on measured data which may deviate according to the application.  
Fusing Characteristics:  $\leq 1 \Omega$




**NFR25** This graph is based on measured data which may deviate according to the application.  
Fusing Characteristics:  $1 \Omega \leq R \leq 15 \Omega$

### PULSE LOADING CAPABILITIES




**NFR25** Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max}$ ) as a function of pulse duration ( $t_i$ ),  $0.22 \Omega \leq R \leq 1 \text{ k}\Omega$




**NFR25** Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max}$ ) as a function of pulse duration ( $t_i$ ),  $15 \Omega \leq R \leq 15 \text{ k}\Omega$




### PULSE LOADING CAPABILITIES



NFR25 Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{U}_{max.}$ ) as a function of pulse duration ( $t_i$ )




NFR25 Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max.}$ ) as a function of pulse duration ( $t_i$ )




NFR25H Pulse on a regular basis; maximum permissible peak pulse power ( $\hat{P}_{max.}$ ) as a function of pulse duration ( $t_i$ )




### APPLICATION INFORMATION



NFR25 Hot-spot temperature rise ( $\Delta T$ ) as a function of dissipated power




NFR25 Hot-spot temperature rise ( $\Delta T$ ) as a function of dissipated power



Minimum distance from resistor body to PCB. = 1 mm

NFR25 Temperature rise ( $\Delta T$ ) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting



Minimum distance from resistor body to PCB. = 1 mm

NFR25 Temperature rise ( $\Delta T$ ) at the lead end (soldering point) as a function of dissipated power at various lead lengths after mounting

### TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with IEC 60115-1 specification, category LCT/UCT/56 (rated temperature range: Lower category temperature, upper category temperature; damp heat, long term, 56 days). The tests are carried out in accordance with IEC 60068-2-xx test method, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to IEC 60068-1, 5.3.

In the Test Procedures and Requirements table the tests and requirements are listed with reference to the relevant clauses of IEC 60115-1 and IEC 60068-2-xx test methods. A short description of the test procedure is also given. In some instances deviations from the IEC recommendations were necessary for our method of specifying. For inflammability requirements reference is made to IEC 60115-1.

All soldering tests are performed with mildly activated flux.



TEST PROCEDURES AND REQUIREMENTS					
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS	
				NFR01	NFR03
4.4.1		Visual examination		No holes; clean surface; no damage	
4.4.2		Dimensions (outline)	Gauge (mm)	See Dimensions Table	
4.5		Resistance (refer note on first page for measuring distance)	Applied voltage (+ 0 % / - 10 %): $R < 10 \Omega$ : 0.1 V $10 \Omega \leq R < 100 \Omega$ : 0.3 V $100 \Omega \leq R < 1 \text{ k}\Omega$ : 1 V $1 \text{ k}\Omega \leq R < 10 \text{ k}\Omega$ : 3 V $10 \text{ k}\Omega \leq R \leq 15 \text{ k}\Omega$ : 10 V	$R - R_{\text{nom}}$ : max. $\pm 5 \%$	
4.18	20 (Tb)	Resistance to soldering heat	Thermal shock: 10 s; 260 °C; 3 mm from body	$\Delta R$ max.: $\pm (0.25 \% R + 0.05 \Omega)$	
4.29	45 (Xa)	Component solvent resistance	Isopropyl alcohol or H <sub>2</sub> O followed by brushing	No visual damage	
4.17	20 (Ta)	Solderability	2 s; 235 °C: Solder bath method; SnPb40 3 s; 245 °C: Solder bath method; SnAg3Cu0.5	Good tinning ( $\geq 95 \%$ covered); no damage	
		Solderability (after aging)	8 h steam or 16 h, 155 °C; leads immersed 6 mm; for 2 s at 235 °C: Solder bath (SnPb40) for 3 s at 245 °C: Solder bath (SnAg3Cu0.5) method	Good tinning ( $\geq 95 \%$ covered); no damage	
4.7		Voltage proof on insulation	$U_{\text{RMS}} = 500 \text{ V}$ during 1 min; metal block method	No breakdown or flashover	
4.16		Robustness of terminations:			
4.16.2	21 (Ua1)	Tensile all samples	Load 10 N; 10 s	Number of failures $< 10 \times 10^{-6}$	
4.16.3	21 (Ub)	Bending half number of samples	Load 5 N; 4 x 90°	Number of failures $< 10 \times 10^{-6}$	
4.16.4	21 (Uc)	Torsion other half of samples	3 x 360° in opposite directions	No damage $\Delta R$ max.: $\pm (0.25 \% R + 0.05 \Omega)$	
4.20	29 (Eb)	Bump	3 x 1500 bumps in 3 directions; 40 g	No damage $\Delta R$ max.: $\pm (0.25 \% R + 0.05 \Omega)$	
4.22	6 (Fc)	Vibration	Frequency 10 Hz to 500 Hz; displacement 1.5 mm or acceleration 10 g; 3 directions; total 6 h (3 x 2 h)	No damage $\Delta R$ max.: $\pm (0.25 \% R + 0.05 \Omega)$	
4.19	14 (Na)	Rapid change of temperature	30 min at LCT and 30 min at UCT; 5 cycles	No visual damage $\Delta R$ max.: $\pm (0.25 \% R + 0.05 \Omega)$	
4.23		Climatic sequence:			
4.23.2	2 (Ba)	Dry heat	16 h; 155 °C		
4.23.3	30 (Db)	Damp heat (accelerated) 1 <sup>st</sup> cycle	24 h; 55 °C; 90 % to 100 % RH		
4.23.4	1 (Aa)	Cold	2 h; -55 °C		
4.23.5	13 (M)	Low air pressure	2 h; 8.5 kPa; 15 °C to 35 °C		
4.23.6	30 (Db)	Damp heat (accelerated) remaining cycles	5 days; 55 °C; 95 % to 100 % RH	$R_{\text{ins}}$ min. $10^3 \text{ M}\Omega$ $\Delta R$ max.: $\pm (1.5 \% R + 0.1 \Omega)$	
4.24	78 (Cab)	Damp heat (steady state)	56 days; 40 °C; 90 % to 95 % RH; loaded with 0.01 $P_{70}$ (IEC steps: 0 V to 100 V)	$R_{\text{ins}}$ min. $10^3 \text{ M}\Omega$ $\Delta R$ max.: $\pm (1 \% R + 0.05 \Omega)$	
4.25.1		Endurance (at 70 °C)	1000 h; loaded with $P_{70}$ or $U_{\text{max}}$ ; 1.5 h ON and 0.5 h OFF	$\Delta R$ max.: $\pm (1 \% R + 0.05 \Omega)$	
4.25.3		Endurance at upper category temperature	1000 h; no load	$\Delta R$ max.: $\pm (1 \% R + 0.05 \Omega)$	
4.8		Temperature coefficient	Between -55 °C and +155 °C $0.22 \Omega \leq R \leq 4.7 \Omega$ $4.7 \Omega < R \leq 15 \Omega$ $15 \Omega < R \leq 15 \text{ k}\Omega$	$\leq \pm 200 \text{ ppm/K}$ $\leq \pm 200 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$	$\leq \pm 200 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$ $\leq \pm 100 \text{ ppm/K}$
4.12		Noise	IEC 60195	$< 0.1 \mu\text{V/V}$	
4.26		Accidental overload	Cheese-cloth	Non flammable	
4.6.1.1		Insulation resistance	Maximum voltage $U_{\text{max}}$ , DC = 500 V after 1 min; metal block method	$R_{\text{ins}}$ min. $10^4 \text{ M}\Omega$	





### 12NC INFORMATION FOR HISTORICAL CODING REFERENCE

- The resistors have a 12 digit numeric code starting with 23
- The subsequent 7 digits indicate the resistor type and packaging
- The remaining 3 digits indicate the resistance value:
  - The first 2 digits indicate the resistance value
  - The last digit indicates the resistance decade

#### Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
0.22 Ω to 0.91 Ω	7
1 Ω to 9.1 Ω	8
10 Ω to 91 Ω	9
100 Ω to 910 Ω	1
1 kΩ to 9.1 kΩ	2
10 kΩ to 15 kΩ	3

#### 12NC Example

The 12NC of a NFR25 resistor with value 750 Ω, supplied on a bandolier of 1000 units in ammopack is: 2322 205 13751.

12NC (Resistors Type and Packaging)				
TYPE	23.. ... .....			
	BANDOLIER IN AMMOPACK			BANDOLIER ON REEL
	RADIAL TAPED	STRAIGHT LEADS		STRAIGHT LEADS
	2000 UNITS	1000 UNITS	5000 UNITS	5000 UNITS
NFR25	22 204 03...	22 205 13...	22 205 33...	22 205 23...
NFR25H	22 207 03...	22 207 13...	22 207 33...	22 207 23...



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**