



Revision Number: 008.0

Issue date: 08/21/2014

1. PRODUCT AND COMPANY IDENTIFICATION

| | | | |
|----------------------------|---|-----------------------------|--|
| Product name: | LOCTITE® 242™ THREADLOCKER MEDIUM STRENGTH | IDH number: | 135354 |
| Product type: | Anaerobic Sealant | Item number: | 24221 |
| Restriction of Use: | None identified | Region: | United States |
| Company address: | Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067 | Contact information: | Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com |

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN AND EYE IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.

| HAZARD CLASS | HAZARD CATEGORY |
|--------------------|-----------------|
| SKIN IRRITATION | 2 |
| EYE IRRITATION | 2B |
| SKIN SENSITIZATION | 1 |

PICTOGRAM(S)



Precautionary Statements

| | |
|--------------------|---|
| Prevention: | Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves. |
| Response: | IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing. |
| Storage: | Not prescribed |
| Disposal: | Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations. |

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

| Hazardous Component(s) | CAS Number | Percentage* |
|---------------------------|-------------|-------------|
| Polyglycol dimethacrylate | Proprietary | 60 - 100 |

| | | |
|--|-------------|---------|
| Polyglycol oleate | Proprietary | 10 - 30 |
| Saccharin | 81-07-2 | 1 - 5 |
| Silica, amorphous, fumed, crystal-free | 112945-52-5 | 1 - 5 |
| Cumene hydroperoxide | 80-15-9 | 1 - 5 |
| Propane-1,2-diol | 57-55-6 | 1 - 5 |
| Cumene | 98-82-8 | 0.1 - 1 |

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

| | |
|----------------------|---|
| Inhalation: | Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention. |
| Skin contact: | Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention. |
| Eye contact: | Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention. |
| Ingestion: | DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention. |
| Symptoms: | See Section 11. |

5. FIRE FIGHTING MEASURES

| | |
|---|--|
| Extinguishing media: | Water spray (fog), foam, dry chemical or carbon dioxide. |
| Special firefighting procedures: | Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray. |
| Unusual fire or explosion hazards: | Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers. |
| Hazardous combustion products: | Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours. |

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

| | |
|-----------------------------------|---|
| Environmental precautions: | Do not allow product to enter sewer or waterways. |
| Clean-up methods: | Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. |

7. HANDLING AND STORAGE

Handling: Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.

Storage: For safe storage, store between 0 °C (32°F) and 32 °C (89.6 °F). Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

| Hazardous Component(s) | ACGIH TLV | OSHA PEL | AIHA WEEL | OTHER |
|--|--|-------------------------------------|----------------------------------|-------|
| Polyglycol dimethacrylate | None | None | None | None |
| Polyglycol oleate | None | None | None | None |
| Saccharin | None | None | None | None |
| Silica, amorphous, fumed, crystal-free | 10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction. | 20 MPPCF TWA 0.8 mg/m3 TWA | None | None |
| Cumene hydroperoxide | None | None | 1 ppm (6 mg/m3) TWA (SKIN) | None |
| Propane-1,2-diol | None | None | 10 mg/m3 TWA Aerosol. | None |
| Cumene | 50 ppm TWA | 50 ppm (245 mg/m3) PEL (SKIN) | None | None |

Engineering controls: Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection: Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection: Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection: Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves. Butyl rubber gloves. Natural rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: Liquid
Color: Blue
Odor: Mild
Odor threshold: Not available.
pH: Not applicable
Vapor pressure: < 5 mm hg (27 °C (80.6 °F))
Boiling point/range: > 149 °C (> 300.2 °F)
Melting point/ range: Not available.
Specific gravity: 1.1 at 23.9 °C (75.02 °F)
Vapor density: Not available.
Flash point: > 93.3 °C (> 199.94 °F) Tagliabue closed cup
Flame projection: Not applicable
Flammable/Explosive limits - lower: 2.6 % (propylene glycol)
Flammable/Explosive limits - upper: 12.5 % (propylene glycol)

| | |
|---|------------------|
| Autoignition temperature: | Not determined |
| Evaporation rate: | Not available. |
| Solubility in water: | Slight |
| Partition coefficient (n-octanol/water): | Not available. |
| VOC content: | 0.56 %; 6.17 g/l |
| Viscosity: | Not available. |
| Decomposition temperature: | Not available. |

10. STABILITY AND REACTIVITY

| | |
|--|--|
| Stability: | Stable under normal conditions of storage and use. |
| Hazardous reactions: | None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials. |
| Hazardous decomposition products: | Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours. |
| Incompatible materials: | Strong oxidizing agents. Free radical initiators. Strong reducing agents. Alkalis. Oxygen scavengers. Other polymerization initiators. Copper. Iron. Zinc. Aluminum. Rust. |
| Reactivity: | Not available. |
| Conditions to avoid: | Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials. |

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

| | |
|----------------------|---|
| Inhalation: | Inhalation of vapors or mists of the product may be irritating to the respiratory system. |
| Skin contact: | Causes skin irritation. May cause allergic skin reaction. |
| Eye contact: | Causes eye irritation. |
| Ingestion: | May cause gastrointestinal tract irritation if swallowed. |

| Hazardous Component(s) | LD50s and LC50s | Immediate and Delayed Health Effects |
|--|---|--|
| Polyglycol dimethacrylate | None | Allergen, Irritant |
| Polyglycol oleate | None | Irritant |
| Saccharin | None | No Target Organs |
| Silica, amorphous, fumed, crystal-free | None | Nuisance dust |
| Cumene hydroperoxide | None | Allergen, Central nervous system, Corrosive, Irritant, Mutagen |
| Propane-1,2-diol | Oral LD50 (RABBIT) = 18 g/kg Oral LD50 (RAT) = 30 g/kg | Irritant |
| Cumene | Oral LD50 (RAT) = 2.91 g/kg Oral LD50 (RAT) = 1,400 mg/kg Inhalation LC50 (RAT, 4 h) = 8000 ppm | Central nervous system, Irritant, Lung |

| Hazardous Component(s) | NTP Carcinogen | IARC Carcinogen | OSHA Carcinogen (Specifically Regulated) |
|--|----------------|-----------------|--|
| Polyglycol dimethacrylate | No | No | No |
| Polyglycol oleate | No | No | No |
| Saccharin | No | No | No |
| Silica, amorphous, fumed, crystal-free | No | No | No |
| Cumene hydroperoxide | No | No | No |
| Propane-1,2-diol | No | No | No |
| Cumene | No | Group 2B | No |

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis

CERCLA/SARA Section 311/312: Immediate Health, Delayed Health

CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Saccharin (CAS# 81-07-2). Cumene hydroperoxide (CAS# 80-15-9).

CERCLA Reportable quantity: Cumene hydroperoxide (CAS# 80-15-9) 10 lbs. (4.54 kg)

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 08/21/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.