



Revision Number: 004.0

Issue date: 08/07/2014

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE SF 7471 PRIMER known as</b> <b>Loctite(R) Locquic(R) Primer T</b>	<b>IDH number:</b>	135337
<b>Product type:</b>	Primer	<b>Item number:</b>	22477
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** CONTENTS UNDER PRESSURE.  
EXTREMELY FLAMMABLE AEROSOL.  
CAUSES SKIN IRRITATION.  
MAY CAUSE AN ALLERGIC SKIN REACTION.  
CAUSES SERIOUS EYE IRRITATION.  
MAY CAUSE DROWSINESS OR DIZZINESS.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE AEROSOL.	1
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3

**PICTOGRAM(S)**



**Precautionary Statements**

**Prevention:**

Keep away from heat, sparks, open flames, hot surfaces - no smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Avoid breathing mist or spray. Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Contaminated work clothing should not be allowed out of the workplace. Wear eye and face protection. Wear protective gloves.

**Response:**

IF ON SKIN: Wash with plenty of soap and water. IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Call a poison control center or physician if you feel unwell. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

**Storage:**

**Disposal:**

Store in a well-ventilated place. Keep container tightly closed. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Acetone	67-64-1	60 - 100
Isobutane	75-28-5	10 - 30
2-Propanol	67-63-0	5 - 10

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Water should be used to cool closed containers to prevent pressure build-up and possible autoignition or explosion when exposed to extreme heat.
<b>Unusual fire or explosion hazards:</b>	Vapors may accumulate in low or confined areas, travel considerable distance to source of ignition, and flash back. Contents under pressure. Exposure to temperatures above 49°C (120°F) may cause container to burst. Do not puncture or incinerate pressurized containers.

**Hazardous combustion products:**

Oxides of sulfur. Oxides of nitrogen. Irritating organic vapours. Oxides of carbon.

**6. ACCIDENTAL RELEASE MEASURES**

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

**Environmental precautions:**

Do not allow product to enter sewer or waterways.

**Clean-up methods:**

Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

**7. HANDLING AND STORAGE****Handling:**

During use and until all vapors are gone: Keep area ventilated - do not smoke; extinguish all flames, pilot lights, and heaters; turn off stoves, electrical tools and appliances, and any other sources of ignition. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Do not puncture or incinerate pressurized containers. Refer to Section 8.

**Storage:**

For safe storage, store at or below 49 °C (120.2 °F)  
Keep in a cool, well ventilated area away from heat, sparks and open flame.  
Keep container tightly closed until ready for use.

**Shelf Life Statement: Not available.****8. EXPOSURE CONTROLS / PERSONAL PROTECTION**

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Acetone	750 ppm STEL 500 ppm TWA	1,000 ppm (2,400 mg/m3) PEL	None	None
Isobutane	1,000 ppm STEL	None	None	None
2-Propanol	200 ppm TWA 400 ppm STEL	400 ppm (980 mg/m3) PEL	None	None

**Engineering controls:**

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

**Respiratory protection:**

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

**Eye/face protection:**

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

**Skin protection:**

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene, Butyl-rubber, or nitrile-rubber gloves.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Aerosol
<b>Color:</b>	Amber, yellow
<b>Odor:</b>	Acetone
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	172 mm hg Approximately
<b>Boiling point/range:</b>	Not available.
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	0.7953 Base only
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	-8 °C (17.6 °F) Tagliabue closed cup; Estimated
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Partially soluble
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	8.31 %; 106 g/l
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing.
<b>Hazardous decomposition products:</b>	Oxides of sulfur. Irritating organic vapours. Oxides of nitrogen. Oxides of carbon.
<b>Incompatible materials:</b>	Strong oxidizing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Do not puncture, incinerate, or expose to temperatures above 48.9 °C (120 °F). Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

<b>Relevant routes of exposure:</b>	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

### Potential Health Effects/Symptoms

**Inhalation:** May cause dizziness, incoordination, headache, nausea, and vomiting.  
**Skin contact:** Causes skin irritation. May cause allergic skin reaction.  
**Eye contact:** Causes serious eye irritation.  
**Ingestion:** May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Acetone	Oral LD50 (RABBIT) = 5,340 mg/kg Oral LD50 (RAT) = 5,800 mg/kg Oral LD50 (RAT) = 9,800 mg/kg Dermal LD50 (RABBIT) = 20,000 mg/kg Inhalation LC50 (RAT, 8 h) = 50.1 mg/l Inhalation LC50 (RAT, 4 h) = 76 mg/l	Blood, Central nervous system, Irritant, Reproductive
Isobutane	Inhalation LC50 (RAT, 15 min) = 570000 ppm	Cardiac, Central nervous system, Lung
2-Propanol	Oral LD50 (RAT) = 5,045 mg/kg Oral LD50 (RABBIT) = 6,410 mg/kg Oral LD50 (RAT) = 4.7 g/kg Oral LD50 (RABBIT) = 8.0 g/kg Oral LD50 (RABBIT) = 5.03 g/kg Dermal LD50 (RABBIT) = 12,800 mg/kg	Allergen, Blood, Brain, Central nervous system, Irritant, Kidney, Liver, Spleen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Acetone	No	No	No
Isobutane	No	No	No
2-Propanol	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** D001: Ignitable.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Aerosols, flammable  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Aerosols, flammable  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None  
**Exceptions:** ID8000, (Not more than 500 ml), May Qualify as Consumer Commodity

**Water Transportation (IMO/IMDG)**

**Proper shipping name:** AEROSOLS  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None  
**Exceptions:** Limited quantity (Not more than 1 L).

**15. REGULATORY INFORMATION****United States Regulatory Information**

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health, Fire  
**CERCLA/SARA Section 313:** None above reporting de minimis  
**CERCLA Reportable quantity:** Acetone (CAS# 67-64-1) 5,000 lbs. (2,270 kg)  
Isobutane (CAS# 75-28-5) 100 lbs. (45.4 kg)  
2-Propanol (CAS# 67-63-0) 100 lbs. (45.4 kg)  
**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

**Canada Regulatory Information**

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

**16. OTHER INFORMATION**

**This safety data sheet contains changes from the previous version in sections:** New Safety Data Sheet format.

**Prepared by:** Sheila Gines, Regulatory Affairs Specialist

**Issue date:** 08/07/2014

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.