



Revision Number: 004.0

Issue date: 07/02/2014

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	LOCTITE EA E-00CL known as LOCTITE EPOXY ADH E-00CL 50 ML	<b>IDH number:</b>	701949
<b>Product type:</b>	Epoxy resin	<b>Item number:</b>	29289_209522
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** CAUSES SKIN IRRITATION.  
MAY CAUSE AN ALLERGIC SKIN REACTION.  
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear eye and face protection. Wear protective gloves.
<b>Response:</b>	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
<b>Storage:</b>	Not prescribed
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Epoxy resin	Proprietary	60 - 100
Substituted silane	Proprietary	0.1 - 1
Epoxy resin	Proprietary	0.1 - 1

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
<b>Unusual fire or explosion hazards:</b>	In case of fire, keep containers cool with water spray. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
<b>Hazardous combustion products:</b>	Oxides of carbon. Phenolics. Irritating vapors.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

## 7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.
- Storage:** Keep container tightly closed and in a cool, well-ventilated place away from incompatible materials. Store away from heat, sparks, flames, or other sources of ignition. Protect from direct sunlight.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Epoxy resin	None	None	None	None
Substituted silane	None	None	None	None
Epoxy resin	None	None	None	None

- Engineering controls:** Provide adequate ventilation.
- Respiratory protection:** Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Liquid
- Color:** Clear, Yellow
- Odor:** Epoxy
- Odor threshold:** Not available.
- pH:** Not available.
- Vapor pressure:** Not available.
- Boiling point/range:** > 149 °C (> 300.2 °F) (1,013 hPa)
- Melting point/ range:** Not available.
- Specific gravity:** 1.15
- Vapor density:** Not available.
- Flash point:** > 93 °C (> 199.4 °F) Pinsky Martens closed cup
- Flammable/Explosive limits - lower:** Not available.
- Flammable/Explosive limits - upper:** Not available.
- Autoignition temperature:** Not available.
- Evaporation rate:** Not available.
- Solubility in water:** Negligible
- Partition coefficient (n-octanol/water):** Not available.
- VOC content:** < 1 %; < 10 g/l Estimated
- Viscosity:** Not available.
- Decomposition temperature:** Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	Reaction with some curing agents may produce an exothermic reaction which in large masses could cause runaway polymerization.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Phenolics. Irritating vapors.
<b>Incompatible materials:</b>	Strong oxidizing agents. Strong acids. Strong bases. Amines.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Keep away from heat, ignition sources and incompatible materials. Protect from direct sunlight.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

### Potential Health Effects/Symptoms

<b>Inhalation:</b>	Inhalation of vapors or mists of the product may be irritating to the respiratory system.
<b>Skin contact:</b>	Causes skin irritation. May cause allergic skin reaction.
<b>Eye contact:</b>	Causes serious eye irritation.
<b>Ingestion:</b>	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Epoxy resin	None	Allergen, Irritant
Substituted silane	None	Allergen, Irritant
Epoxy resin	None	No Data

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Epoxy resin	No	No	No
Substituted silane	No	No	No
Epoxy resin	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.  
**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Environmentally hazardous substance, liquid, n.o.s. (Bisphenol-A Epichlorhydrin resin)  
**Hazard class or division:** 9  
**Identification number:** UN 3082  
**Packing group:** III

### Water Transportation (IMO/IMDG)

**Proper shipping name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)  
**Hazard class or division:** 9  
**Identification number:** UN 3082  
**Packing group:** III  
**Marine pollutant:** Bisphenol-A Epichlorhydrin resin

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Immediate Health  
**CERCLA/SARA Section 313:** None above reporting de minimis  
**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

### Canada Regulatory Information

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

## 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

**Prepared by:** Sheila Gines, Regulatory Affairs Specialist  
**Issue date:** 07/02/2014

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.