

GA355DR7GB103KY02#

" # " indicates a package specification code.

To be discontinued

General

Safety standard

125℃


Reflow OK


RoHS

REACH

< List of part numbers with package codes >  
GA355DR7GB103KY02L

Shape





|                                       |             |
|---------------------------------------|-------------|
| L size                                | 5.7 ± 0.4mm |
| W size                                | 5.0 ± 0.4mm |
| T size                                | 2.0 ± 0.3mm |
| External terminal width e             | 0.3mm min.  |
| Distance between external terminals g | 4.0mm min.  |
| Size code in inch(mm)                 | 2220 (5750) |

Notes

Please use replacements or Recommended.

References

| Packaging | Specifications        | Minimum quantity |
|-----------|-----------------------|------------------|
| L         | 180mm Embossed taping | 1000             |

| Mass (typ.) |       |
|-------------|-------|
| 1 piece     | 290mg |
| 180mm Reel  | 347g  |

Specifications

|  |               |
|--|---------------|
| Capacitance                                      | 10000pF ± 10% |
| Rated voltage                                    | 250Vac        |
| Temperature characteristics (complied standard)  | X7R(EIA)      |
| Capacitance change rate                          | ± 15.0%       |
| Temperature range of temperature characteristics | -55 to 125    |
| Operating temperature range                      | -55 to 125    |

⚠ Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.