


CECC (€) 40401-010 Qualified Thin Film Chip Resistors




Utilizing proven expertise in Thin Film resistors, VISHAY provides a CECC qualified chip with the same reliability and stability found in QPL resistors. These chips are available in a wide range of sizes, values and performance characteristics.

CONSTRUCTION



FEATURES





 Tight TCR < 10 ppm/°C, and in lot tracking < 5 ppm/°C in (-55 °C, +155 °C temperature range)



- Very low noise < 35 dB and voltage coefficient 0.1 ppm/V
- Non-inductive
- Laser trimmed down to 0.1 %
- Wraparound resistance less than 0.01 Ω
- Antistatic waffle-pack or tape and reel packaging available
- High stability (0.05 % 1000 h at Pn at +70 °C)
- Withstand moisture resistance test of AEC-Q200
- Conform to EN 140401 804
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

Note

This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS						
MODEL	SIZE	RESISTANCE RANGE (1) (2) Ω	RATED POWER Pn W	LIMITING ELEMENT VOLTAGE (UL) V	TOLERANCE ± %	TEMPERATURE COEFFICIENT ± ppm/°C
RV =	0505	100 to 260K	0.125	50	0.1, 0.5, 1, 2, 5	10, 25
RV 들	0603	100 to 260K	0.125	50	0.1, 0.5, 1, 2, 5	10, 25
RV 들	0805	100 to 300K	0.200	50	0.1, 0.5, 1, 2, 5	10, 25
RV €	1206	100 to 1M	0.330	75	0.1, 0.5, 1, 2, 5	10, 25

Notes

(1) Extended resistance range on request

(2) For ohmic range versus tolerance and TCR, see detailed table

CLIMATIC SPECIFICATIONS		
Operating temperature range	-55 °C to +155 °C	
Storage temperature range	-55 °C to +155 °C	

MECHANICAL SPECIFICATIONS			
Resistive material	Nichrome		
Substrate material	Alumina		
Plating	Tin lead over nickel or tin silver over nickel or gold over nickel		
Marking resistance to solvents	Per CECC Specs		


OHMIC RANGE VS. TOLERANCE AND TCR				
CASE SIZE	OHMIC RANGE Ω	TOLERANCE %	TCR ppm/°C	
0505	100 < 500	0.5; 1; 2; 5	10, 25	
0505	500 to 260K	0.1; 0.5; 1; 2; 5	10, 25	
0603	100 < 500	0.5; 1; 2; 5	10, 25	
0603	500 to 260K	0.1; 0.5; 1; 2; 5	10, 25	
0805	100 < 500	0.5; 1; 2; 5	10, 25	
0805	500 to 300K	0.1; 0.5; 1; 2; 5	10, 25	
1206	100 < 500	0.5; 1; 2; 5	10, 25	
1206	500 to 1M	0.1; 0.5; 1; 2; 5	10, 25	

TECHNICAL SPECIFICATIONS				
TEST	SPECIFICATIONS	CONDITIONS		
Absolute TCR	E: ± 25 ppm/°C Y: ± 10 ppm/°C	-55 °C to +155 °C		
Absolute tolerance	\pm 0.1 %, \pm 0.5 %, \pm 1 %, \pm 2 %, \pm 5 % (R \geq 500 Ω)			
Absolute tolerance	$\pm 0.5 \%$, $\pm 1 \%$, $\pm 2 \%$, $\pm 5 \%$ ($R \ge 100 \Omega$)			
Voltage coefficient	0.1 ppm/V			
Noise	-35 dB typical			
Thermal EMF	< 0.1 μV/°C			
Load life stability	± (0.1 % Rn ⁽³⁾ ± 0.05 Ω)	1000 h Pn at +70 °C		

Note

(3) Rn: Nominal resistance





POPULAR OPTION

AEC-Q200 moisture resistance

Option to order: 0058: Specific production process to withstand 85 °C/85 % RH at Pn/10

ENVIRONMENTAL TEST				
TEST	CONDITIONS	VALUES AND DRIFTS (ΔR/R ± %)		
1231	CONDITIONS	CECC REQUIREMENTS	TYPICAL PERFORMANCE	
Overload	6.25 x rated power / 2 s (or 2 UL)	$0.05~\%~{ m Rn}^{~(2)} + 0.05~\Omega$	0.01 % Rn ⁽²⁾	
Climatic sequences (1)	Climatic sequences ⁽¹⁾ -55 °C / +155 °C 5 moisture cycles		0.02 % Rn ⁽²⁾	
Thermal shock ⁽¹⁾ -55 °C / +155 °C 5 cycles 30 min		$0.05~\%~{ m Rn}^{~(2)} + 0.05~\Omega$	0.02 % Rn ⁽²⁾	
Load life ⁽¹⁾ +70 °C/Pn 1000 h		0.1 % Rn $^{(2)}$ + 0.05 Ω	0.05 % Rn ⁽²⁾	
Resistance to solder heat +260 °C/ 10 s		$0.05~\%~{ m Rn}^{~(2)} + 0.05~\Omega$	0.02 % Rn ⁽²⁾	
	+40 °C / 93 % HR Pn / 10	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.01 % Rn ⁽²⁾	
Moisture resistance (1)	AEC-Q200 ⁽³⁾ 85 °C / 85 % RH / Pn / 10 1000 h	0.5 % + 0.05 Ω	Max. < 0.3 % + 0.05 Ω	
High temperature storage	1000 h at + 155 °C	0.1 % Rn ⁽²⁾ + 0.05 Ω	0.05 % Rn ⁽²⁾	
Bending ⁽¹⁾	10 bends / 2 mm / 5 s	0.05 % Rn ⁽²⁾ + 0.05 Ω	0.02 % Rn ⁽²⁾	

SPECIFIC CONDITIONS DUE TO TERMINATION TYPE				
TEST	COND	ITIONS	VALUES AND DRIFTS	
1231	B; G	N	VISHAY REQUIREMENTS	TYPICAL PERFORMANCE
Solderability	+235 °C/2 s Sn60Pb40 alloy	+245 °C/3 s Sn97Ag3 alloy	VISUAL INSPECTION	
High T° reflow profile	N/A	+255 °C/40 s (on parts)	0.02 % Rn ⁽²⁾ + 0.05 Ω 0.01 % Rn ⁽²⁾ + 0.05 Ω	

Notes

⁽¹⁾ Test requiring parts to be mounted on PCB will be performed with the requirement that termination alloy will be the same as solder paste alloy. Gold termination will be tested as B termination

⁽²⁾ Rn: Nominal Resistance Pn: Nominal Power

⁽³⁾ Option to order: 0058










PACKAGING INFORMATION				
	NUMBER OF PIECES PER PACKAGE			
SIZE	WAFFLE PACK	TAPE AN	ND REEL	TAPE
	(2" x 2")	Min.	Max.	WIDTH
0505	100		4000	
0603	100	100	5000	8 mm
0805	100	100	4000	(0.315")
1206	140		4000	

DERATING CURVE











Vishay Sfernice

CODIFICATION OF PACKAGING		
CODE 18	PACKAGING	
WAFFLE PACK		
W	100 min., 1 mult	
WA	100 min., 100 mult (available only in size 1206)	
PLASTIC TAPE (Standard for all	sizes.)	
Т	100 min., 1 mult	
TA	100 min., 100 mult	
ТВ	250 min., 250 mult	
TC	500 min., 500 mult	
TD	1000 min., 1000 mult	
TE	2500min., 2500 mult	
TF	Full tape (quantity depending on size of chips)	
PAPER TAPE (Available for 0603, 0805, and 1206. Please consult Vishay Sfernice for other sizes.)		
PT	100 min., 1 mult	
PA	100 min., 100 mult	
PB	250 min., 250 mult	
PC	500 min., 500 mult	
PD	1000 min., 1000 mult	
PE	2500min., 2500 mult	
PF	Full tape (quantity depending on size of chips)	



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000