

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0670689000](#)

Status: **Active**

Overview: [Consumer USB Products](#)

Description: Universal Serial Bus (USB) Shielded I/O Type B Receptacle, Right Angle, with Kinked Solder Tabs, Color White, Gold (Au) Flash Plating, Tray Pack, Lead-Free

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-67998-0000 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980


UL E29179

General

Product Family I/O Connectors
Series [67068](#)
Application Wire-to-Board
Comments Single
Component Type Receptacle
MolexKits Yes
Overview [Consumer USB Products](#)
Product Name USB 2.0
Type B
UPC 822348723041

Physical

Boot Color N/A
Circuits (Loaded) 4
Circuits (maximum) 4
Color - Resin Natural
Flammability 94V-0
Gender Receptacle
Lock to Mating Part Yes
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 3.827/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 2.80mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Panel Mount No
Pitch - Mating Interface 2.50mm
Pitch - Termination Interface 2.50mm
Plating min - Mating 0.051µm
Plating min - Termination 1.905µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating 0°C to +50°C
Termination Interface: Style Through Hole
Waterproof / Dustproof No



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[67068](#) Series

Mates With

USB Type B Plug

Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V (RMS)

Solder Process Data

Lead-free Process Capability	WAVE
Process Temperature max. C	260

Material Info**Reference - Drawing Numbers**

Product Specification	PS-67998-0000
Sales Drawing	SD-67068-003, SD-67068-004

This document was generated on 03/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION