




Optocoupler, Phototransistor Output, with Base Connection, 300 V BV_{CEO}

5 C




DESCRIPTION

The SFH640 is an optocoupler with very high BV_{CER} , a minimum of 300 V. It is intended for telecommunications applications or any DC application requiring a high blocking voltage.

FEATURES

- Good CTR linearity with forward current
- Low CTR degradation





Isolation test voltage: 5300 V_{RMS}

Low coupling capacitance

- High common mode transient immunity
- Phototransistor optocoupler 6 pin DIP package with base connection
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC

AGENCY APPROVALS

- UL1577, file no. E52744 system code H or J, double protection
- DIN EN 60747-5-2 (VDE 0884) available with option 1
- CSA 93751
- BSI IEC 60950; IEC 60065

ORDERING INFORMATION								
S F H 6 4 PART NUMBER	O - # X O # # T T CTR PACKAGE OPTION TAPE AND REEL OPTION Option 7 Option 7 Option 9 > 0.1 mm							
AGENCY CERTIFIED/PACKAGE	CTR (%)							
AGENOT GENTIFIED/FAGRAGE	10 mA							
UL, CSA, BSI	63 to 125 100 to 200							
DIP-6	SFH640-2 SFH640-3							
SMD-6, option 7	SFH640-2X007 SFH640-3X007T ⁽¹⁾							
VDE, UL, CSA, BSI	63 to 125 100 to 200							
SMD-6, option 9	- SFH640-3X019T ⁽¹⁾							

Notes

- Additional options may be possible, please contact sales office.
- (1) Also available in tubes, do not put T on the end.

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION SYMBOL VALUE						
INPUT							
Reverse voltage		V_{R}	6.0	V			
DC forward current		I _F	60	mA			
Surge forward current	t _p ≤ 10 µs	I _{FSM}	2.5	Α			
Total power dissipation		P _{diss}	100	mW			



www.vishay.com

Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
OUTPUT							
Collector emitter voltage		V_{CEO}	300	V			
Collector base voltage		V_{CBO}	300	V			
Emitter base voltage		V_{EBO}	7.0	V			
Collector current		I _C	50	mA			
Surge collector current	$t_p \le 10 \text{ ms}$	I _C	100	mA			
Total power dissipation		P _{diss}	300	mW			
COUPLER							
Isolation test voltage		V_{ISO}	5300	V_{RMS}			
between emitter and detector		VISO	7500	V_{PK}			
Isolation resistance	$V_{IO} = 500 \text{ V}, T_{amb} = 25 ^{\circ}\text{C}$	R _{IO}	≥ 10 ¹²	Ω			
isolation resistance	V_{IO} = 500 V, T_{amb} = 100 °C	R _{IO}	≥ 10 ¹¹	Ω			
Insulation thickness between emitter and detector			≥ 0.4	mm			
Creepage distance			≥ 7	mm			
Clearance distance			≥ 7	mm			
Comparative tracking index per DIN IEC 112/VDE 0303, part 1		CTI	175				
Storage temperature range		T _{stg}	- 55 to + 150	°C			
Operating temperature range		T _{amb}	- 55 to + 100	°C			
Soldering temperature (1)	max. 10 s, dip soldering: distance to seating plane ≥ 1.5 mm	T _{sld}	260	°C			

Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
	TEST CONDITION	FANI	STWIBOL	IVIIIV.	IIF.	IVIAA.	ONT
INPUT	T		ı		1		
Forward voltage	I _F = 10 mA		V_V		1.1	1.5	V
Reverse voltage	$I_R = 10 \mu A$		V_R	6			V
Reverse current	V _R = 6 V		I _R		0.01	10	μA
Capacitance	V _F = 0 V, f = 1 MHz		Co		25		pF
Thermal resistance			R _{thja}		750		K/W
OUTPUT							
Collector emitter breakdown voltage	$I_{CE} = 1 \text{ mA},$ $R_{BE} = 1 \text{ M}\Omega$		BV _{CER}	300			V
Voltage emitter base	I _{EB} = 10 μA		BV _{BEO}	7			V
Collector emitter capacitance	V _{CE} = 10 V, f = 1 MHz		C _{CE}		7		pF
Collector base capacitance	V _{CB} = 10 V, f = 1 MHz		C _{CB}		8		pF
Emitter base capacitance	V _{EB} = 5 V, f = 1 MHz		C _{EB}		38		pF
Thermal resistance			R _{thja}		250		K/W
COUPLER							
Coupling capacitance			C _C		0.6		pF
Saturation voltage collector	$I_F = 10 \text{ mA}, I_C = 3.2 \text{ mA}$	SFH640-2	V _{CEsat}		0.25	0.4	V
emitter	$I_F = 10 \text{ mA}, I_C = 5 \text{ mA}$	SFH640-3	V _{CEsat}		0.25	0.4	V
Collector emitter leakage current	$V_{CE} = 200 \text{ V}, R_{BE} = 1 \text{ M}\Omega$		I _{CER}		1	100	nA

Note

Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering
evaluation. Typical values are for information only and are not part of the testing requirements.



Vishay Semiconductors

CURRENT TRANSFER RATIO (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Current transfer ratio	$I_F = 10 \text{ mA}, V_{CE} = 10 \text{ V}$	SFH640-2	I _C /I _F	63		125	%
	I _F = 1 mA, V _{CE} = 10 V	SFH640-2	I _C /I _F	22	45		%
	$I_F = 10 \text{ mA}, V_{CE} = 10 \text{ V}$	SFH640-3	I_{C}/I_{F}	100		200	%
	$I_F = 1 \text{ mA}, V_{CE} = 10 \text{ V}$	SFH640-3	I _C /I _F	34	70		%

SWITCHING CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Turn-on time	$I_C = 2 \text{ mA}, R_L = 100 \Omega, V_{CC} = 10 \text{ V}$	t _{on}		5		μs	
Rise time	I_C = 2 mA, R_L = 100 Ω , V_{CC} = 10 V	t _r		2.5		μs	
Turn-off time	$I_C = 2 \text{ mA}, R_L = 100 \Omega, V_{CC} = 10 \text{ V}$	t _{off}		6		μs	
Fall time	$I_C = 2 \text{ mA}, R_L = 100 \Omega, V_{CC} = 10 \text{ V}$	t _f		5.5		μs	

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Switching Times Measurement Test Circuit and Waveform




Fig. 3 - Current Transfer Ratio (typ.)




Fig. 2 - Switching Times Measurement Test Circuit and Waveform




Fig. 4 - Diode Forward Voltage (typ.)



Vishay Semiconductors




Fig. 5 - Output Characteristics (typ.)




Fig. 6 - Output Characteristics (typ.)




Fig. 7 - Transistor Capacitances (typ.)




Fig. 8 - Collector-Emitter Leakage Current (typ.)




Fig. 9 - Permissible Loss Diode





Fig. 10 - Permissible Power Dissipation

Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters








DIP-6A

PACKAGE DIMENSIONS in inches (millimeters)



Note

The information in this document provides generic information but for specific information on a product the appropriate product datasheet should be used.



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000