

Capacitor, ceramic, 220 pF, +/-5% Tol, 100 V, COG



| Dimensions (mm) |           |               |
|-----------------|-----------|---------------|
| Symbol          | Dimension | Tolerance     |
| D               | 2.31      | MAX           |
| L               | 4.32      | MAX           |
| LL              | 25.4      | +0.025/-0.076 |
| F               | 0.51      | +0.025/-0.076 |

| Packaging Specifications |      |
|--------------------------|------|
| Package Kind:            | T&R  |
| Package Size:            | 12in |
| Package Quantity:        | 5000 |

| General Information      |                 |
|--------------------------|-----------------|
| Supplier:                | KEMET           |
| Application:             | General Purpose |
| Temperature Coefficient: | COG             |
| Body Type:               | Axial Conformal |
| Lead Type:               | Wire Leads      |
| Termination Type:        | Tin (Sn)        |
| RoHS:                    | Yes             |

| Specifications         |           |
|------------------------|-----------|
| Capacitance:           | 220 pF    |
| Voltage:               | 100 V     |
| Tolerance:             | +/-5%     |
| Temperature Range:     | -55/+125C |
| Failure Rate:          | N/A       |
| Dissipation Factor:    | 0.1%      |
| Insulation Resistance: | 100 GOhm  |
| Dielectric Strength:   | 250 V     |