

Capacitor, ceramic, 2200 pF, +/-10% Tol, 100 V, X7R



| Dimensions (mm) | | |
|-----------------|-----------|---------------|
| Symbol | Dimension | Tolerance |
| D | 2.31 | MAX |
| L | 4.32 | MAX |
| LL | 25.4 | +0.025/-0.076 |
| F | 0.51 | +0.025/-0.076 |

| Packaging Specifications | |
|--------------------------|------|
| Package Kind: | T&R |
| Package Size: | 12in |
| Package Quantity: | 5000 |

| General Information | |
|--------------------------|-----------------|
| Supplier: | KEMET |
| Application: | General Purpose |
| Temperature Coefficient: | X7R |
| Body Type: | Axial Conformal |
| Lead Type: | Wire Leads |
| Termination Type: | Tin (Sn) |
| RoHS: | Yes |

| Specifications | |
|------------------------|-----------|
| Capacitance: | 2200 pF |
| Voltage: | 100 V |
| Tolerance: | +/-10% |
| Temperature Range: | -55/+125C |
| Failure Rate: | N/A |
| Dissipation Factor: | 2.5% |
| Insulation Resistance: | 100 GOhm |
| Dielectric Strength: | 250 V |