


Capacitor, ceramic, 0.33 uF, +/-20% Tol, 50 V, Z5U



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	3.05	MAX
L	4.32	MAX
LL	25.4	+0.025/-0.076
F	0.51	+0.025/-0.076

Packaging Specifications	
Package Kind:	T&R
Package Size:	12in
Package Quantity:	5000

General Information	
Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	Z5U
Body Type:	Axial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	0.33 uF
Voltage:	50 V
Tolerance:	+/-20%
Temperature Range:	+10/+85C
Failure Rate:	N/A
Dissipation Factor:	4%
Insulation Resistance:	300 MOhm
Dielectric Strength:	125 V