

KEMET Part Number: C1206C475J8NACTU
(C1206C475J8NAC7800)

Capacitor, Ceramic, SMD, MLCC, High Temperature, Temperature Stable, 4.7 uF, +/-5% Tol, 10 V, X8L, 1206 (3216 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	X8L
Part Type Description:	SMD, MLCC, High Temperature, Temperature Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1.6	+/-0.20
B	0.5	+/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2000

Specifications	
Capacitance:	4.7 uF
Voltage:	10 V
Tolerance:	+/-5%
Temperature Range:	-55/+150C
Dissipation Factor:	3.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	110 MOhm
Dielectric Strength:	25 V
Miscellaneous:	Note: Referee time for X8L dielectric for this part number is 1000 hours