

# Fluke 721 and 721Ex Precision Pressure Calibrators

## Technical Data

### Pressure calibration and temperature measurement for custody transfer applications

The Fluke 721 and 721Ex Precision Pressure Calibrators with dual isolated pressure sensors are the ideal tool for gas custody transfer applications allowing you to take simultaneous static and differential pressure measurements with a single tool.

### Product highlights

The 721 and 721Ex can be configured by selecting either a 16 PSI (1.1 bar) or 36 psi (2.48 bar) low pressure sensor then add any of 7 high pressure ranges including 100, 300, 500, 1000, 1500, 3000 or 5000 psi (6.9, 20, 24.5, 69, 103.4, 200, 345 bar).

- Intrinsically Safe (721Ex version only) – IECEx and Atex Ex ia IIB T3 Gb (Zone 1)
- Ideal for gas flow calibration (custody transfer) applications
- Two isolated, stainless steel, pressure sensors with 0.025 % accuracy
- Switch test on both pressure inputs
- Pressure displayed in the user's choice of 19 engineering units
- Pt100 RTD input for temperature measurement, (probe optional)
- Measures 4 to 20 mA signals
- Internal 24 V loop power supply can power a transmitter under test (721 models only)
- Measure up to 30 V dc, check 24 V loop power supplies (721 models only)
- Extend pressure measurement range with connection to one of 50 external 750 series pressure modules from 0 to 1 inH<sub>2</sub>O to 10,000 psi (2.5 mBar to 690 bar) (721 models only)
- Large backlit graphic display can display up to three inputs simultaneously
- Store five instrument setups for recall and use



## Specifications 1-year

		Low pressure sensor			High pressure sensor		
Model	Description	Range sensor 1	Resolution sensor 1	Accuracy sensor 1	Range sensor 2	Resolution sensor 2	Accuracy sensor 2
<b>Fluke-721-1601</b> <b>Fluke-721Ex-1601</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 100 PSIG	-14 psi to +16 psi -0.97 bar to 1.1 bar	0.001 psi, 0.0001 bar	0.025% of full scale	-12 psi to +100 psi -0.83 bar to 6.9 bar	0.01 psi 0.0001 bar	0.025% of full scale
<b>Fluke-721-1603</b> <b>Fluke-721Ex-1603</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 300 PSIG				-12 psi to +300 psi -0.83 bar to 20 bar	0.01 psi 0.001 bar	
<b>Fluke-721-1605</b> <b>Fluke-721Ex-1605</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 500 PSIG				-12 psi to +500 psi -0.83 bar to 34.5 bar	0.01 psi 0.001 bar	
<b>Fluke-721-1610</b> <b>Fluke-721Ex-1610</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 1000 PSIG				0 psi to +1000 psi 0.00 bar to 69 bar	0.1 psi 0.001 bar	
<b>Fluke-721-1615</b> <b>Fluke-721Ex-1615</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 1500 PSIG				0 psi to +1500 psi 0.00 bar to 103.4 bar	0.1 psi 0.001 bar	
<b>Fluke-721-1630</b> <b>Fluke-721Ex-1630</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 3000 PSIG				0 psi to +3000 psi 0.00 bar to 200 bar	0.1 psi 0.01 bar	
<b>Fluke-721-1650</b> <b>Fluke-721Ex-1650</b>	Dual Sensor Pressure Calibrator, 16 PSIG, 5000 PSIG				0 psi to +5000 psi 0.00 bar to 345 bar	0.1 psi 0.01 bar	0.035% of full scale
<b>Fluke-721-3601</b> <b>Fluke-721Ex-3601</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 100 PSIG	-14 psi to +36 psi -0.97 bar to 2.48 bar	0.001 psi, 0.0001 bar	0.025% of full scale	-12 to +100 psi -0.83 bar to 6.9 bar	.01 psi 0.0001 bar	0.025% of full scale
<b>Fluke-721-3603</b> <b>Fluke-721Ex-3603</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 300 PSIG				-12 psi to +300 psi -0.83 bar to 20 bar	0.01 psi 0.001 bar	
<b>Fluke-721-3605</b> <b>Fluke-721Ex-3605</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 500 PSIG				-12 psi to +500 psi -0.83 bar to 34.5 bar	0.01 psi 0.001 bar	
<b>Fluke-721-3610</b> <b>Fluke-721Ex-3610</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 1000 PSIG				0 psi to +1000 psi 0.00 bar to 69 bar	0.1 psi 0.001 bar	
<b>Fluke-721-3615</b> <b>Fluke-721Ex-3615</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 1500 PSIG				0 psi to +1500 psi 0.00 bar to 103.4 bar	0.1 psi 0.01 bar	
<b>Fluke-721-3630</b> <b>Fluke-721Ex-3630</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 3000 PSIG				0 psi to +3000 psi 0.00 bar to 200 bar	0.1 psi 0.01 bar	
<b>Fluke-721-3650</b> <b>Fluke-721Ex-3650</b>	Dual Sensor Pressure Calibrator, 36 PSIG, 5000 PSIG				0 psi to +5000 psi 0.00 bar to 345 bar	0.1 psi 0.01 bar	0.035% of full scale

General specifications	
Instrument setup recall	Last used on power-up
Environmental	Operating temperature -10 °C to +50 °C (Fluke 721) Operating temperature -10 °C to +45 °C (Fluke 721Ex) Storage temperature (without batteries) -20 °C to +60 °C
Altitude	2,000 meters
Ingress protection	IP-40
Power requirements	6.0 v dc
Battery life	>35 hours, typical usage
Batteries required	(4) Standard AA cells
Dimensions (HxWxD)	7.9" X 4.3" X 2.3" (20 cm X 11 cm X 5.8 cm)
Weight	0.539 kg (1 lb 3 oz)
Connectors/ports pressure	Two, 1/8 in NPT, 750P Series Pressure Module (721 models only); RTD Probe

Electrical and temperature measurement 1-year			
Function	Range	Resolution	Accuracy
mA measure	0 to 24 mA	0.001 mA	±0.015% of rdg ±0.002mA
VDC measure**	0 to 30 VDC	0.001V	±0.015% of rdg ±0.002V
*Temperature measure (RTD/Ohms)	-40 °C to 150 °C (-40 °F to 302 °F)	0.01 °C, 0.01 °F	±0.015% of rdg ±0.02 ohms; ±0.1 °C (±0.2 °F) ±0.25 °C (±0.45 °F) combined uncertainty when using 720 RTD probe accessory
Loop power supply**	24V	N/A	24 mA @ 24V
*Temperature measurement requires optional Fluke-720RTD Pt-100 RTD probe available as an accessory **721 models only			

Temperature effect
No effect on accuracy on all functions from 15 °C to 35 °C
Add ± 0.002 % F.S./°C for temps outside of 15 °C to 35 °C

## Ordering information

<b>Fluke-721-1601</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1601</b>	16 PSIG, 100 PSIG
<b>Fluke-721-1603</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1603</b>	16 PSIG, 300 PSIG
<b>Fluke-721-1605</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1605</b>	16 PSIG, 500 PSIG
<b>Fluke-721-1610</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1610</b>	16 PSIG, 1000 PSIG
<b>Fluke-721-1615</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1615</b>	16 PSIG, 1500 PSIG
<b>Fluke-721-1630</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1630</b>	16 PSIG, 3000 PSIG
<b>Fluke-721-1650</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-1650</b>	16 PSIG, 5000 PSIG
<b>Fluke-721-3601</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3601</b>	36 PSIG, 100 PSIG
<b>Fluke-721-3603</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3603</b>	36 PSIG, 300 PSIG
<b>Fluke-721-3605</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3605</b>	36 PSIG, 500 PSIG
<b>Fluke-721-3610</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3610</b>	36 PSIG, 1000 PSIG
<b>Fluke-721-3615</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3615</b>	36 PSIG, 1500 PSIG
<b>Fluke-721-3630</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3630</b>	36 PSIG, 3000 PSIG
<b>Fluke-721-3650</b>	Dual Sensor Pressure Calibrator
<b>Fluke-721Ex-3650</b>	36 PSIG, 5000 PSIG
<b>Fluke-720RTD</b>	RTD Probe for Fluke-721, 721Ex and 719Pro
<b>Fluke-720URTD</b>	Universal RTD adapter for Fluke-721, 721Ex and 719Pro

### Included:

- Soft case
- Four (4) AA batteries
- Manual
- Traceable calibration certificate
- Test leads

### 721Ex Approval Details

ATEX	Ex ia IIB T3 Gb (Ta= -10... +45 °C)
	KEMA 10 ATEX 0168X
IECEX	Ex ia IIB T3 Gb (Ta= -10... +45 °C)
	II 2 G IECEX CSA 10.0013X

### User selectable pressure engineering units

psi, bar, mbar, kPa, kgcm<sup>2</sup>, cmH<sub>2</sub>O@4°C, cmH<sub>2</sub>O@20°C, mH<sub>2</sub>O@4°C, mH<sub>2</sub>O@20°C, inH<sub>2</sub>O@4°C, inH<sub>2</sub>O@20°C, inH<sub>2</sub>O@60°F, mmHg@0°C, inHg@0°C, ftH<sub>2</sub>O@4°C, ftH<sub>2</sub>O@20°C, ftH<sub>2</sub>O@60°F

**Fluke.** *Keeping your world up and running.*<sup>®</sup>

**Fluke Europe B.V.**  
P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
Web: [www.fluke.co.uk](http://www.fluke.co.uk)

**For more information call:**  
In Europe/M-East/Africa  
+31 (0)40 267 5100 or  
Fax +31 (0)40 267 5222

**Fluke (UK) Ltd.**  
52 Hurricane Way  
Norwich, Norfolk  
NR6 6JB  
United Kingdom  
Tel.: +44 (0) 20 7942 0700  
Fax: +44 (0) 20 7942 0701  
E-mail: [industrial@uk.fluke.nl](mailto:industrial@uk.fluke.nl)  
Web: [www.fluke.co.uk](http://www.fluke.co.uk)

©2015 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
04/2015 Pub\_ID: 12085-eng

**Modification of this document is not permitted without written permission from Fluke Corporation.**