
## Resistors

# Water Insoluble Nitride Thin Film **Precision Chip Resistors**

#### **WIN Series**

- TaN thin film technology
- Inherent moisture protection superior to that of passivated nichrome chip resistors
- High stability in humid and polluted environments
- Typical 85°C, 85%RH biased humidity 2000 hour stability <0.1%</li>
- Typical moisture resistance stability ±100ppm
- Precision ±0.05% tolerance and ±15ppm/°C
- Anti-sulfur terminations






All Pb-free parts comply with EU Directive 2011/65/EU (RoHS2)

## **Electrical Data**

		T0603	T0805	T1206		
Power rating @ 70°C	watts 0.1 0.25 0.33					
Resistance range	ohms	5R to 100K	5R to 267K	5R to 1M0		
Limiting element voltage (maximum voltage)	Vdc or rms	75	100	200		
Resistance tolerance	%	±0.05 ±0.1 ±0.5 ±1				
TCR	ppm/°C	±15 ±25 ±50				
Standard values		E24, E96, E192				
Ambient temperature range	°C	-65 to +150				

## **Physical Data**

Dimensions in mm & (inch) and weight in mg								
	L	W	Т	С	А	Wt. nom		
T0603	1.58 ± 0.15 (0.062 ± 0.006)	$0.80 \pm 0.10$ (0.031 ± 0.004)	0.45 ± 0.10 (0.018 ± 0.004)	0.27 ± 0.20 (0.011 ± 0.008)	0.34 ± 0.20 (0.013 ± 0.008)	2.0		
T0805	2.02 ± 0.15 (0.080 ± 0.006)	1.28 ± 0.15 (0.050 ± 0.006)	0.45 ± 0.10 (0.018 ± 0.004)	0.31 ± 0.20 (0.012 ± 0.008)	0.40 ± 0.20 (0.016 ± 0.008)	4.3		
T1206	3.15 ± 0.15 (0.124 ± 0.006)	1.57 ± 0.15 (0.062 ± 0.006)	0.50 ± 0.15 (0.020 ± 0.006)	0.45 ± 0.25 (0.018 ± 0.010)	0.52 ± 0.25 (0.020 ± 0.010)	9.6		



### Construction

Conductors, thin film resistive element and epoxy outer protection are applied to an alumina substrate. The chips are supplied with wrap-around terminations suitable for soldering. The terminations have an electroplated nickel barrier and either 100% matt tin or 60/40 SnPb finish.

## Marking & Solvent Resistance

WIN resistors have no marking on the component body. The body protection is resistant to all normal cleaning solvents suitable for printed circuits









**WIN Series** 

# **Manufacturing Capabilities Data**



## **Performance Data**

		ΔR		
Test	Method	MIL-PRF-55342	WIN actual	
		Limits (max)	performance (typ)	
Thermal Shock	MIL-PRF-55342 4.8.3 (MIL-STD-202 107G cond. F: 5 cycles in air, +150 / -65°C)	± 0.1%	± 0.025%	
Low Temp. Operation	MIL-PRF-55342 4.8.5 (-65°C)	± 0.1%	± 0.02%	
Short Time Overload	MIL-PRF-55342 4.8.6 (lesser of 6.25 x Pr or 2 x LEV for 5 seconds)	± 0.1%	± 0.02%	
High Temp. Exposure	MIL-PRF-55342 4.8.7 (+150°C for 100 hours)	± 0.1%	± 0.05%	
Resistance to Solder Heat	MIL-PRF-55342 4.8.8	± 0.2%	± 0.02%	
Moisture Resistance	MIL-PRF-55342 4.8.9 (MIL-STD-202 106G: 10 cycles, 65±2°C, 95±5% RH)	± 0.2%	± 0.01%	
Load Life	MIL-PRF-55342 4.8.11 (MIL-STD-202 108A: Pr at 70°C for 2000 hours)	± 0.5%	± 0.08%	
Biased Damp Heat	85°C, 85%RH, 10% Pr bias, for 2000 hours	N/A	± 0.08%	
Flower of Sulfur	ASTM B-809 (modified) 105°C Dry, 1000 Hours	Р	ass	




### **Resistors**

#### Water Insoluble Nitride Thin Film Precision Chip Resistors



#### **WIN Series**



# **Ordering Procedure**


This product has two valid part numbers:

European (Welwyn) Part Number: WINT1206LF031001B3 (1206, ±25ppm/°C, 1 kilohm ±0.1%, Pb-free)



1	2	3	4	5	6		7	
Series	Туре	Termination	TCR	Value	Tolerance		Packi	ng
WIN	T0603	PB = SnPb	11 = ±15ppm/°C	3 digits + multiplier	$A = \pm 0.05\%$	٦	Гаре & re	eel
	T0805	LF = Pb free	03 = ±25ppm/°C		B = ±0.1%	3	3000/reel	Standard
	T1206		02 = ±50ppm/°C	values <100 ohms	D = ±0.5%	Blank	1000/reel	
					F = 1%			

USA (IRC) Part Number: WIN -T1206LF-03-1001-B3 (1206, ±25ppm/°C, 1 kilohm ±0.1%, Pb-free)



1	2	3	4	5	6		7	
Series	Туре	Termination	TCR	Value	Tolerance		Packir	ng
WIN	T0603	PB = SnPb	11 = ±15ppm/°C	3 digits + multiplier	$A = \pm 0.05\%$	Tape & reel		eel
	T0805	LF = Pb free	03 = ±25ppm/°C	R = ohms for	$B = \pm 0.1\%$	3	3000/reel	Standard
	T1206		$02 = \pm 50 \text{ppm/}^{\circ}\text{C}$	values <100 ohms	$D = \pm 0.5\%$	Blank	1000/reel	
			•		F = 1%			<u> </u>