

#### Pushbutton, flush, red 0, momentary

Part no.

Article no.

Catalog No.

M22-D-R-X0 216605 M22-D-R-X0Q



**Delivery programme** 

Product range		RMQ-Titan (drilling dimensions 22.5 mm)
Basic function		Pushbutton actuators
Single unit/Complete unit		Single unit
Design		Flat
		momentary
Button plate		
button plate		red
Button plate		
		inscribed
Degree of Protection		IP67, IP69K
Front ring		Bezel: titanium
Connection to SmartWire-DT		Yes, with SWD-RMQ connections
Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1		
Minimum force for positive opening	N	0
Front dimensions		22 x 22

# **Technical data**

delleral			
Standards			IEC/EN 60947 VDE 0660
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	>5
Operating frequency	Operations/h		≤ <sub>3600</sub>
Actuating force		n	≦ <sub>5</sub>
Climatic proofing			Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Ambient temperature			
Open		°C	-25 - +70
Storage		°C	- 40 - + 80
Mounting position			As required
Mechanical shock resistance		g	30 Shock duration 11 ms Sinusoidal according to IEC 60068-2-27
Indoor and protected outdoor installation			

## Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	In	Α	0
Heat dissipation per pole, current-dependent	P <sub>vid</sub>	W	0
Equipment heat dissipation, current-dependent	P <sub>vid</sub>	W	0
Static heat dissipation, non-current-dependent	P <sub>vs</sub>	W	0
Heat dissipation capacity	$P_{\text{diss}}$	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70

IEC/EN 61439 design verification	
10.2 Strength of materials and parts	
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Please enquire
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	Not applicable.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### **Technical data ETIM 6.0**

Low-voltage industrial components (EG000017) / Front element for push button (EC000221)


Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for push-button actuators (ecl@ss8.1-27-37-12-10 [AKF028011])


Colour buttonRedNumber of command positions11Construction type lens80m2Hole diametermm2Width openingmm2Height meter openingmm6Degree of protection (IP), front sidemm167Suitable for illuminationmm167With protection covermm160Suitching function latchingmm160Spring-returnmm160With front ringmm160Material front ringmm160Gour front ringmm160Hongmm160Housemm160Ho	[AKF028011])		
Construction type lensRoundHole diametermm22Width openingmm22Height meter openingmm6Degree of protection (IP), front sideIP67Type of buttonFlatSuitable for illuminationNoWith protection coverNoLabelledYesSwitching function latchingNoSpring-returnYesWith front ringYesMaterial front ringPlasticHatch of the protection of	Colour button		Red
Hole diameter Width opening mm 22 Height meter opening mm 6 Degree of protection (IP), front side IP67 Type of button Suitable for illumination No With protection cover Labelled Switching function latching No Spring-return With front ring Material front ring Material front ring Page 1	Number of command positions		1
Width opening mm 22 Height meter opening mm 6 Degree of protection (IP), front side IP67 Type of button Suitable for illumination No With protection cover No Labelled Switching function latching No Spring-return Yes With front ring Plastic	Construction type lens		Round
Height meter opening mm 6 Degree of protection (IP), front side IP67 Type of button Flat Suitable for illumination No With protection cover No Labelled Yes Switching function latching No Spring-return Yes With front ring Yes Material front ring Plastic	Hole diameter	mm	22
Degree of protection (IP), front side  Type of button  Suitable for illumination  With protection cover  Labelled  Switching function latching  Spring-return  With front ring  Material front ring  Material front ring  IP67  Flat  Flat  No  No  No  No  Yes  Yes  Plastic	Width opening	mm	22
Type of button  Suitable for illumination  With protection cover Labelled  Switching function latching  Spring-return  With front ring  Material front ring  Flat  No  No  No  No  Yes  Plastic	Height meter opening	mm	6
Suitable for illumination  No With protection cover  Labelled  Switching function latching  Spring-return  With front ring  Material front ring  No  No  No  Yes  Yes  Plastic	Degree of protection (IP), front side		IP67
With protection cover Labelled Yes Switching function latching Spring-return With front ring Material front ring No Plastic	Type of button		Flat
Labelled Yes Switching function latching No Spring-return Yes With front ring Yes Material front ring Plastic	Suitable for illumination		No
Switching function latching  No Spring-return  With front ring  Material front ring  No Yes  Yes  Plastic	With protection cover		No
Spring-return Yes With front ring Yes Material front ring Plastic	Labelled		Yes
With front ring  Material front ring  Yes  Plastic	Switching function latching		No
Material front ring Plastic	Spring-return		Yes
	With front ring		Yes
Colour front ring Chrome	Material front ring		Plastic
	Colour front ring		Chrome


# Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	012528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified

### **Dimensions**







### **Additional product information (links)**

#### IL04716002Z (AWA1160-1745) RMQ-Titan System

IL04716002Z (AWA1160-1745) RMQ-Titan System

 $ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL04716002Z2015\_02.pdf$