

Product information

10.8v LXT COMBI DRILL/DRIVER



Satisfying the professional's needs

HP330DZ

| | |
|-----------------------------|------------------------|
| Capacity in Steel | 10 mm |
| Capacity in Wood | 21 mm |
| Chuck Capacity | 10 mm |
| Capacity in Masonry | 8 mm |
| Blows per Minute (Hi) - ipm | 0 - 22,500 ipm |
| Blows per Minute (Lo) - ipm | 0 - 6000 ipm |
| No Load Speed (Hi) | 0 - 1500 rpm |
| No Load Speed (Lo) | 0 - 400 rpm |
| Voltage | 10.8 v |
| Max Torque S/H | 12 / 24 Nm |
| Torque Settings | 18 + Drill Mode |
| Battery Type | Lithium-ion |
| Charging Time | 50 min |
| Battery Quantity (1.3Ah) | 2 |
| Vibration: Drilling | 2.5 m/sec ² |
| Vibration K factor | 1.5 m/sec ² |
| Body only machine | 1 |
| Net weight | 1.1 kg |



STANDARD EQUIPMENT: 194550-6 10.8V Li-ion Battery, DC10WA 7.2V-10.8V BATTERY CHARGER

- 10mm (3/8") Single-sleeve keyless chuck
- With 2-speed gear selection
- Ergonomically designed handle with rubberised soft grip fits your hand perfectly to provide maximum control and comfort.
- Single LED job light with pre-glow function
- Variable speed control by trigger
- Hammer drill mode has been added for drilling holes in mortar etc

Details correct as of: 24-5-2016

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com