

KEMET Part Number: C1206C100JGGACTU
(C1206C100JGGAC7800)

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 10 pF, +/-5% Tol, 2000 V, COG, 1206 (3216 metric)



CeramicChipSMDNoS
© 2011 IntelMicro Inc.
All rights reserved

General Information

Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)

Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1	+/-0.10
B	0.5	+/-0.25

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2500

Specifications

Capacitance:	10 pF
Voltage:	2000 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	2400 V