

KEMET Part Number: C1206C105K3NACTU
(C1206C105K3NAC7800)

Capacitor, Ceramic, SMD, MLCC, High Temperature, Temperature Stable, 1 uF, +/-10% Tol, 25 V, X8L, 1206 (3216 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	X8L
Part Type Description:	SMD, MLCC, High Temperature, Temperature Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1	+/-0.10
B	0.5	+/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2500

Specifications	
Capacitance:	1 uF
Voltage:	25 V
Tolerance:	+/-10%
Temperature Range:	-55/+150C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	500 MOhm
Dielectric Strength:	62.5 V
Miscellaneous:	Note: Referee time for X8L dielectric for this part number is 1000 hours