




LED Retrofit 5.5W S15



Product Overview

LED retrofit lamps are direct replacements for conventional incandescent, halogen, and compact fluorescent (CFL) lamps. LEDs deliver higher lumens per watt (lm/W) which means significant energy savings while lasting more than ten times longer than incandescent sources. With their directional light, instant on and ability to dim, LEDs are fast becoming the light source of choice

Features

- More eco-valued.
- Excellent optical design, alike SMT appearance.
- Reliable IC solution, automatic production.

Safety and Maintenance

- Switch off supply before installing or removing lamp.
- Allow to cool before handling.
- Do not use in totally enclosed fittings as this will reduce lamp life.
- Do not dispose of in household waste.
- Dispose of in appropriate section of local civic amenity site or recycling centre.

Specifications – S15 Strip Tube

SKU	S9218
Lamp	S15 Strip Tube
Nominal Power (W)	5.5
Voltage	220-240Vac 50Hz
Current (mA)	40
Nominal Luminous Flux (lm)	550
CCT (K)	2700K warm White
Nominal Lifetime (h)	15000
Dimmable	No
Switching Cycles	15000
Warm-up time to 60% (S)	Instant
Length (mm)	284
Diameter (mm)	26
Mercury (mg)	0
Clean-up instructions	See website
Retrofit	Yes
Equivalent Wattage (W)	50
Rated Power (W)	5.5
Rated Luminous Flux (lm)	550
Rated Lifetime (h)	15000
Power Factor	0.54
Rated Peak Candelas (cd)	
Lumen Maintenance Factor at	
Nominal Lifetime	15000
CRI	>80
Start Time (s)	Instant
Ambient Temperature Range (°C)	-20 to 40

Energy Label – S15 Strip Tube


Energy Class	A+
Energy Consumption (kWh/1000h)	5.50(6)*

* The kWh/1000h value published on the energy label is required to be rounded up to an integer according to the EU implementing directive on Energy Labelling. The value to 2 decimal places is given for reference

Product Markings – S15 Strip Tube

Voltage	220-240Vac 50Hz
Nominal Power (W)	5.5
Current (mA)	40
CE Mark	Yes
WEEE Mark	Yes
Batch Code	Yes

Dimensions



Photometric Information

2700K

