

HANNSpree

HANNSpad

HANNSpad 101 Hercules 10.1" IPS Wi-Fi



10.1" / 25,65 cm

Part. No.: SN1ATP1B

SIZE, RESOLUTION



10.1" IPS Panel
25,65 cm



1280 x 800

CPU, RAM MEMORY



QuadCore CPU
ARM Cortex A53
64 bit



1 GB DDR

CAMERA, STORAGE



Dual Camera
2MP/2MP



16 GB

Wi-Fi, CONNECTIVITY



Dual Band
WLAN 802.11 a/b/g/n
2.4 / 5 GHz



Mini HDMI Output

[Technical Specifications >>>](#)

HANNSpree

HANNSpad

Name / Part Nr.	HANNSpad Hercules / SN1ATP1B
Screen Size	25.65 cm / 10.1 Inch
Resolution (H x V)	1280 x 800, 16:10 Aspect Ratio
Viewing Angle	178° (V) / 178° (H)
Touchscreen Type	Multi Point Capacitive Touch Panel
CPU	Quad Core CPU MT8163 Cortex ARM A53 64 bit, 1.3 GHz
GPU	Mali 720 MP2
Memory	1GB RAM
Storage Internal	16GB eMMC NAND FLASH
Storage External	Micro-SD/Micro-SDHC Card, max. 32GB
WLAN	Wi-Fi IEEE 802.11 a/b/g/n 2.4/5GHz (802.11ac is not supported)
Bluetooth	Bluetooth 4.1
Camera	Front 2MP / Rear 2MP
Microphone	Built-in
Speakers	Built-in, Stereo Speakers 2 x 0.8W, 8 ohm
Headphone Output	3.5mm Stereo Earphone
HDMI	Mini HDMI (V. 1.4 Type C)
GPS	Yes
G-Sensor	Yes
3 Axis Accelerometer	Yes
OTG	Yes
Battery Type	Li-Ion Battery 5.000 mAh, 3.7 Volt
Battery Life	>5 hours (720p Video playback, Wi-Fi Off, Brightness 60%, Webcam off)
Power Adaptor	DC 5V, 2A

Operating Temperature	0 ~ 45° Celsius
Operating Humidity	10 ~ 85%
Case Material	Plastic with rubber painting
Product Dimensions	249.1 x 172.1 x 10.7 (W x H x D mm)
Packaging Dimensions	285 x 210 x 55 (W x H x D mm)
Net Weight	700 grams
Gross Weight	1007 grams
Control Keys	Power, Volume +/-, Reset
Operating System	Android 5.1 (Lollipop)
UI Language	Android default
Accessory	1 Power Adaptor with EU and UK clips, 1 USB Cable (120 cm), 1 OTG Cable (5 cm), Quick Start Guide, Warranty Card
Certification	CE EMC, R&TTE, LVD, RoHS, REACH, WEEE
Packaging	Color retail box
EAN Code	4711404021589

PART. NO.:
SN1ATP1B



4 711404 021589 >