

KEMET Part Number: C0805C153J1HACTU
(C0805C153J1HAC7800)

Capacitor, Ceramic, SMD, MLCC, High Temperature, Ultra-Stable, 0.015 uF, +/-5% Tol, 100 V, X8R, 0805 (2012 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	0805 (2012 metric)
Temperature Coefficient:	X8R
Part Type Description:	SMD, MLCC, High Temperature, Ultra-Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	2	+/-0.2
W	1.25	+/-0.2
T	1.25	+/-0.15
B	0.5	+/-0.25
S	0.75	MIN

Specifications	
Capacitance:	0.015 uF
Voltage:	100 V
Tolerance:	+/-5%
Temperature Range:	-55/+150C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	66.67 GOhm
Dielectric Strength:	250 V
Miscellaneous:	Note: Referee time for X8R dielectric for this part number is 1000 hours

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2500