


KEMET Part Number: C0603C153G3GACTU
(C0603C153G3GAC7867)

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0.015 uF, +/-2% Tol, 25 V, COG, 0603 (1608 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	0603 (1608 metric)
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.15
W	0.8	+/-0.15
T	0.8	+/-0.07
B	0.35	+/-0.15
S	0.7	MIN

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Paper Tape
Package Quantity:	4000

Specifications	
Capacitance:	0.015 uF
Voltage:	25 V
Tolerance:	+/-2%
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	66.67 GOhm
Dielectric Strength:	62.5 V