

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 48 V DC/100 W

Product Description

UNO POWER power supplies with basic functionality

Thanks to their high power density, compact UNO POWER power supplies are the ideal solution for loads up to 100 W, particularly in compact control boxes. The power supply units are available in various performance classes and overall widths. Their high degree of efficiency and low idling losses ensure a high level of energy efficiency.

Product Features

- Flexible mounting by simply snapping onto the DIN rail
- More space in the control cabinet with up to 20 % higher power density
- Maximum energy efficiency, thanks to over 90 % efficiency and extremely low idling losses under 0.3 W



Key Commercial Data

| | |
|--------------------------------------|---------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 360.0 g |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------|-------|
| Width | 55 mm |
| Height | 90 mm |
| Depth | 84 mm |

Ambient conditions

| | |
|---|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 70 °C (> 55° C derating : 2.5%/K) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Technical data

Ambient conditions

| | |
|--|-----------------------------------|
| Max. permissible relative humidity (operation) | ≤ 95 % (at 25 °C, non-condensing) |
| Noise immunity | EN 61000-6-2:2005 |

Input data

| | |
|-------------------------------------|---|
| Nominal input voltage range | 100 V AC ... 240 V AC |
| Input voltage range | 85 V AC ... 264 V AC |
| AC frequency range | 45 Hz ... 65 Hz |
| Current consumption | 1.7 A (120 V AC) |
| | 1 A (230 V AC) |
| Inrush surge current | < 40 A (typical) |
| Power failure bypass | > 25 ms (120 V AC) |
| | > 90 ms (230 V AC) |
| Input fuse | 4 A (slow-blow, internal) |
| Choice of suitable circuit breakers | 6 A ... 16 A (Characteristics B, C, D, K) |
| Type of protection | Transient surge protection |
| Protective circuit/component | Varistor |

Output data

| | |
|--|---|
| Nominal output voltage | 48 V DC ±1 % |
| Nominal output current (I _N) | 2.1 A U _{in} = 85 V AC ... 264 V AC (-25°C ... 55°C) |
| Derating | 55 °C ... 70 °C (2.5%/K) |
| Connection in parallel | Yes, for redundancy and increased capacity |
| Connection in series | Yes |
| Control deviation | < 1 % (change in load, static 10 % ... 90 %) |
| | < 2 % (Dynamic load change 10 % ... 90 %, 10 Hz) |
| | < 0.1 % (change in input voltage ±10 %) |
| Residual ripple | < 40 mV _{PP} (with nominal values) |
| Output power | 100 W |
| Typical response time | < 1 s |
| Maximum power dissipation in no-load condition | < 0.4 W |
| Power loss nominal load max. | < 11 W |

General

| | |
|---------------------------------|--|
| Net weight | 0.34 kg |
| Efficiency | > 90 % (for 230 V AC and nominal values) |
| Insulation voltage input/output | 4 kV AC (type test) |
| | 3 kV AC (routine test) |
| Protection class | II (in closed control cabinet) |
| MTBF (IEC 61709, SN 29500) | > 1010000 h (40°C) |

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Technical data

General

| | |
|-----------------------|--|
| Mounting position | horizontal DIN rail NS 35, EN 60715 |
| Assembly instructions | Alignable: 0 mm horizontally, 30 mm vertically |

Connection data, input

| | |
|---------------------------------------|---------------------|
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Conductor cross section AWG min. | 24 |
| Conductor cross section AWG max. | 14 |
| Stripping length | 8 mm |
| Screw thread | M3 |

Connection data, output

| | |
|---------------------------------------|---------------------|
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Conductor cross section AWG min. | 24 |
| Conductor cross section AWG max. | 14 |
| Stripping length | 8 mm |
| Screw thread | M3 |

Standards and Regulations

| | |
|--|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2004/108/EC |
| Noise immunity | EN 61000-6-2:2005 |
| Connection in acc. with standard | CUL |
| Standards/regulations | EN 61000-4-2 |
| | EN 61000-4-3 |
| | EN 61000-4-4 |
| | EN 61000-4-5 |
| | EN 61000-4-6 |
| | EN 61000-4-11 |
| Standard – Electrical equipment of machines | EN 60204-1 |
| Standard - Electrical safety | IEC 60950-1/VDE 0805 (SELV) |
| Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations | EN 50178/VDE 0160 (PELV) |

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Technical data

Standards and Regulations

| | |
|--|---|
| Standard – Safety extra-low voltage | IEC 60950-1 (SELV) and EN 60204-1 (PELV) |
| Standard - Safe isolation | DIN VDE 0100-410 |
| Standard – Limitation of mains harmonic currents | EN 61000-3-2 |
| UL approvals | UL/C-UL listed UL 508 |
| | UL/C-UL Recognized UL 60950 |
| | UL ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D T4 (Hazardous Location) |
| Vibration (operation) | < 15 Hz, amplitude ± 2.5 mm (according to IEC 60068-2-6) |
| | 15 Hz ... 150 Hz, 2.3g, 90 min. |
| Low Voltage Directive | Conformance with LV directive 2006/95/EC |
| Approval - requirement of the semiconductor industry with regard to mains voltage dips | EN 61000-4-11 |
| Information technology equipment - safety (CB scheme) | CB Scheme |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27040702 |
| eCl@ss 4.1 | 27040702 |
| eCl@ss 5.0 | 27049002 |
| eCl@ss 5.1 | 27049002 |
| eCl@ss 6.0 | 27049002 |
| eCl@ss 7.0 | 27049002 |
| eCl@ss 8.0 | 27049002 |
| eCl@ss 9.0 | 27040701 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001039 |
| ETIM 4.0 | EC000599 |
| ETIM 5.0 | EC002540 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211502 |
| UNSPSC 7.0901 | 39121004 |
| UNSPSC 11 | 39121004 |
| UNSPSC 12.01 | 39121004 |
| UNSPSC 13.2 | 39121004 |

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Approvals

Approvals

Approvals

UL Recognized / UL Listed / cUL Recognized / cUL Listed / IECB CB Scheme / cULus Recognized / cULus Listed


Ex Approvals

UL Listed / cUL Listed / cULus Listed


Approvals submitted

Approval details

UL Recognized 

UL Listed 

cUL Recognized 

cUL Listed 

IECEE CB Scheme 

cULus Recognized 

Power supply unit - UNO-PS/1AC/48DC/100W - 2902996

Approvals



Accessories

Accessories

Redundancy module

Redundancy module - TRIO-DIODE/48DC/2X10/1X20 - 2866527



Redundancy module with function monitoring, 48 V DC, 2x 10 A, 1x 20 A

Drawings

Block diagram

