COMPONENT SPECIFICATION

Name Ferrite Chip EMI Suppressors COMPOSITE SPECIFICATION 1/SPEC# MFB-321611-0075PQ 2

1. SCOPE

This specification applies to the MFB-321611 series Ferrite Chip EMI suppressors.

2. STANDARD ATMOSPHERIC CONDITIONS

Unless otherwise specified the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 20±15 ℃ Relative humidity : 30~70%

If there may be any doubt on the results, measurements shall be made within

the following limits:


Ambient temperature : 25±5°C Relative humidity : 30~70%

3. RATINGS

		*	
IMPEDANCE (Ω)	DC RESISTANCE	RATED CURRENT	
AT100 MHz 500mV	(Ω) Max	(mA) Max	
75±25%	0.03	3000	

lphaThe maximum rated current : the DC current value having temperature increased 40 $^{\circ}$ C after thru DC current 2 hours at ambient temperature.

4. DIMENSION



OPERATING TEMP. RANGE: -55° C ~ +125 $^{\circ}$ C STORAGE TEMP. RANGE: -10° C ~ +40 $^{\circ}$ C

L	W	1	Α
3.2±0.2	1.6±0.2	1.1±0.2	0.4~1
(0.126±0.008)	(0.063±0.008)	(0.043±0.008)	(0.016~0.039)

5. The place of origin:

Taiwan

ı						
	HISTORY	DATE	REVISION		SIGN.	SIGN.
	PLANNED BY	CHECKED BY	APPROVED BY			
		7				
١						
١						

COMPONENT SPECIFICATION

Name Ferrite Chip EMI Suppressors
MFB-321611-0075PQ COMPOSITE SPECIFICATION
SPEC#

