

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0009503081</u>
Status:	Active
Overview:	KK® Interconnect System - Molex
Description:	KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 8 Circuits

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)
[Packaging Specification PK-2139-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

General	
Product Family	Crimp Housings
Series	<u>2139</u>
Application	Power, Wire-to-Board
Overview	<u>KK® Interconnect System - Molex</u>
Product Name	KK® 396
UPC	800753614062

Physical

Circuits (maximum)	8
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.064/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Old Part Number 2139-8A

Reference - Drawing Numbers

Packaging Specification	PK-2139-001
Product Specification	PS-08-50
Sales Drawing	SD-2139



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series

2139 Series

Mates With

KK® 396 Headers: 41771, 41772,
41791, 41792, 42491, 42492, KK® 396
Breakaway Headers: 41661, 41662, 41671
41672

Use With

2478 Crimp Terminals for 18-24 AWG, 2578
Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION