

# GV3P40

## TeSys GV3-Circuit breaker-thermal-magnetic - 30...40A - EverLink BTR connectors



### Main

Commercial Status	Commercialised
Range	TeSys
Product name	TeSys GV3
Device short name	GV3P
Product or component type	Circuit breaker
Circuit breaker application	Motor protection
Poles description	3P
Network type	AC
Utilisation category	Category A conforming to IEC 60947-2 AC-3 conforming to IEC 60947-4-1
Network frequency	50/60 Hz conforming to IEC 60947-4-1
Breaking capacity	Icu = 12 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 6 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 50 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 100 kA at 230/240 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	50 % at 690 V AC 50/60 Hz conforming to IEC 60947-2 50 % at 500 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 440 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2
Thermal protection adjustment range	30...40 A
Trip unit technology	Thermal-magnetic
Magnetic tripping current	560 A

### Complementary

Mounting mode	By clips By screws
Mounting support	Plate Rail
Mounting position	Horizontal Vertical
Motor power kW	37 kW at 690 V AC 50/60 Hz 22 kW at 500 V AC 50/60 Hz 18.5 kW at 400/415 V AC 50/60 Hz
Control type	Rotary knob
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ith] conventional free air thermal current	40 A conforming to IEC 60947-4-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Power dissipation per pole	8 W
Mechanical durability	50000 cycles

Electrical durability	50000 cycles for AC-3 at 440 V In
Operating rate	25 cyc/h
Rated duty	Continuous conforming to IEC 60947-4-1
Connections - terminals	EverLink BTR screw connectors 2 cable(s) 1...25 mm <sup>2</sup> - cable stiffness : flexible - with cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm <sup>2</sup> - cable stiffness : flexible - without cable end EverLink BTR screw connectors 2 cable(s) 1...25 mm <sup>2</sup> - cable stiffness : solid
Tightening torque	5...8 N.m - on EverLink BTR screw connectors- cable 35 mm <sup>2</sup> 5 N.m - on EverLink BTR screw connectors- cable 25 mm <sup>2</sup>
Mechanical robustness	Vibrations 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 Shocks opened 30 Gn for 11 ms conforming to IEC 60068-2-27 Shocks closed 15 Gn for 11 ms conforming to IEC 60068-2-27
Suitability for isolation	Yes conforming to IEC 60947-1
Phase failure sensitivity	Yes conforming to IEC 60947-4-1
Height	132 mm
Width	55 mm
Depth	136 mm
Product weight	0.96 kg

## Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-2 EN/IEC 60947-4-1 UL 508 type E CSA C22.2 No 14-05 type E
Product certifications	ATEX BV CCC CSA DNV GL GOST LROS (pending) RINA UL
Protective treatment	TH
IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK09
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	960 °C conforming to IEC 60695-2-1
Operating altitude	3000 m