

## Safety data sheet

### SECTION 1. Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name **SILCOSET® 151**

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Adhesive sealant.**

#### 1.3. Details of the supplier of the safety data sheet

Name **ACC Silicones LTD**  
Full address **Amber House Showground Road**  
District and Country **TA6 6AJ Bridgwater (Somerset)**  
**England**  
Tel. **+44(0)1278411400**  
Fax **+44(0)1278411444**

e-mail address of the competent person responsible for the Safety Data Sheet **sean.stoodley@acc-silicones.com**

#### 1.4. Emergency telephone number

For urgent inquiries refer to **For all enquiries except Sweden: +44(0)1278411400****Sweden: Ring 112 vid inträffade förgiftningstillbud och begär giftinformation - dygnet runt.****Ring 08-331231 i mindre brådskande fall - dygnet runt. Allmänna och förebyggande frågor om akuta förgiftningar besvaras vardagar kl 9-17.**

### SECTION 2. Hazards identification.

#### 2.1. Classification of the substance or mixture.

The product is classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements). The product thus requires a safety datasheet that complies with the provisions of EC Regulation 1907/2006 and subsequent amendments.

Any additional information concerning the risks for health and/or the environment are given in sections 11 and 12 of this sheet.

Hazard classification and indication:

Eye irritation, category 2  
Skin irritation, category 2H319  
H315Causes serious eye irritation.  
Causes skin irritation.

#### 2.2. Label elements.

Hazard labelling pursuant to EC Regulation 1272/2008 (CLP) and subsequent amendments and supplements.

Hazard pictograms:

Signal words: **Warning**

Hazard statements:

**H319** Causes serious eye irritation.  
**H315** Causes skin irritation.

Precautionary statements:

**P264** Wash . . . thoroughly after handling.



# ACC Silicones LTD

## SILCOSET® 151

Revision nr.17  
Dated 07/12/2015  
Printed on 12/02/2016  
Page n. 2 / 8

EN

### SECTION 2. Hazards identification. ... / >>

**P280** Wear protective gloves / eye protection / face protection.  
**P302+P352** IF ON SKIN: wash with plenty of water / . . .  
**P332+P313** If skin irritation occurs: Get medical advice / attention.

#### 2.3. Other hazards.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

### SECTION 3. Composition/information on ingredients.

#### 3.1. Substances.

Information not relevant.

#### 3.2. Mixtures.

Contains:

Identification.	Conc. %.	Classification 1272/2008 (CLP).
<b>METHYLSILANETRIYL-TRIACETATE</b>		
CAS. 4253-34-3	1 - 3	Acute Tox. 4 H302, Skin Corr. 1B H314, EUH014
EC. 224-221-9		
INDEX.		
<b>ACETIC ACID</b>		
CAS. 64-19-7	0 - 0.1	Flam. Liq. 3 H226, Skin Corr. 1A H314, Note B
EC. 200-580-7		
INDEX. 607-002-00-6		

Note: Upper limit is not included into the range.  
The full wording of hazard (H) phrases is given in section 16 of the sheet.

### SECTION 4. First aid measures.

#### 4.1. Description of first aid measures.

EYES: Remove contact lenses, if present. Wash immediately with plenty of water for at least 30-60 minutes, opening the eyelids fully. Get medical advice/attention.

SKIN: Remove contaminated clothing. Rinse skin with a shower immediately. Get medical advice/attention.

INGESTION: Have the subject drink as much water as possible. Get medical advice/attention. Do not induce vomiting unless explicitly authorised by a doctor.

INHALATION: Get medical advice/attention immediately. Remove victim to fresh air, away from the accident scene. If the subject stops breathing, administer artificial respiration. Take suitable precautions for rescue workers.

#### 4.2. Most important symptoms and effects, both acute and delayed.

For symptoms and effects caused by the contained substances, see chap. 11.

#### 4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

### SECTION 5. Firefighting measures.

#### 5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT

Extinguishing substances are: carbon dioxide, foam, chemical powder. For product loss or leakage that has not caught fire, water spray can be used to disperse flammable vapours and protect those trying to stem the leak.

UNSUITABLE EXTINGUISHING EQUIPMENT

Do not use jets of water. Water is not effective for putting out fires but can be used to cool containers exposed to flames to prevent explosions.

#### 5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Excess pressure may form in containers exposed to fire at a risk of explosion. Do not breathe combustion products.

#### 5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.



# ACC Silicones LTD

## SILCOSET® 151

Revision nr.17  
Dated 07/12/2015  
Printed on 12/02/2016  
Page n. 3 / 8

EN

### SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

## SECTION 6. Accidental release measures.

### 6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

### 6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

### 6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. Evaluate the compatibility of the container to be used, by checking section 10.

Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Check incompatibility for container material in section 7. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

### 6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

## SECTION 7. Handling and storage.

### 7.1. Precautions for safe handling.

Ensure that there is an adequate earthing system for the equipment and personnel. Avoid contact with eyes and skin. Do not breathe powders, vapours or mists. Do not eat, drink or smoke during use. Wash hands after use. Avoid leakage of the product into the environment.

### 7.2. Conditions for safe storage, including any incompatibilities.

Store only in the original container. Store in a ventilated and dry place, far away from sources of ignition. Keep containers well sealed.

Keep the product in clearly labelled containers. Avoid overheating. Avoid violent blows. Keep containers away from any incompatible materials, see section 10 for details.

### 7.3. Specific end use(s).

Information not available.

## SECTION 8. Exposure controls/personal protection.

### 8.1. Control parameters.

Regulatory References:

CZE	Česká Republika	Nářízení vlády č. 361/2007 Sb. kterým se stanoví podmínky ochrany zdraví při práci
DEU	Deutschland	MAK-und BAT-Werte-Liste 2012
DNK	Danmark	Graensevaerdier per stoffer og materialer
ESP	España	INSHT - Límites de exposición profesional para agentes químicos en España 2015
FIN	Suomi	HTP-arvot 2012. Haitallisiksi tunnetut pitoisuudet - Sosiaali- ja terveystieteiden tutkimuskeskus julkaisu 2012:5
FRA	France	JORF n°0109 du 10 mai 2012 page 8773 texte n° 102
HUN	Magyarország	50/2011. (XII. 22.) NGM rendelet a munkahelyek kémiai biztonságáról
NLD	Nederland	Databank of the social and Economic Council of Netherlands (SER) Values, AF 2011:18
NOR	Norge	Veiledning om Administrative normer for forurensning i arbeidsatmosfære
POL	Polska	ROZPORZĄDZENIE MINISTRA PRACY I POLITYKI SPOŁECZNEJ z dnia 16 grudnia 2011r
SVK	Slovensko	NARIADENIE VLÁDY Slovenskej republiky z 20. júna 2007
SWE	Sverige	Occupational Exposure Limit Values, AF 2011:18
EU	OEL EU	Directive 2009/161/EU; Directive 2006/15/EC; Directive 2004/37/EC; Directive 2000/39/EC.
	TLV-ACGIH	ACGIH 2014

### SECTION 8. Exposure controls/personal protection. ... / >>

#### ACETIC ACID

##### Threshold Limit Value.

Type	Country	TWA/8h		STEL/15min	
		mg/m3	ppm	mg/m3	ppm
TLV	CZE	25		35	
AGW	DEU	25	10	50	20
MAK	DEU	25	10	50	20
TLV	DNK	25	10		
VLA	ESP	25	10	37	15
HTP	FIN	13	5	25	10
VLEP	FRA			25	10
AK	HUN	25		25	
MAC	NLD		10		
TLV	NOR	25	10		
NDS	POL	15		30	
NPHV	SVK	25	10		
MAK	SWE	13	5	25	10
OEL	EU	25	10		
TLV-ACGIH		25	10	37	15

Legend:

(C) = CEILING ; INHAL = Inhalable Fraction ; RESP = Respirable Fraction ; THORA = Thoracic Fraction.

#### 8.2. Exposure controls.

As the use of adequate technical equipment must always take priority over personal protective equipment, make sure that the workplace is well aired through effective local aspiration. Personal protective equipment must be CE marked, showing that it complies with applicable standards.

Provide an emergency shower with face and eye wash station.

##### HAND PROTECTION

Protect hands with category III work gloves (see standard EN 374).

The following should be considered when choosing work glove material: compatibility, degradation, failure time and permeability.

The work gloves' resistance to chemical agents should be checked before use, as it can be unpredictable. The gloves' wear time depends on the duration and type of use.

##### SKIN PROTECTION

Wear category II professional long-sleeved overalls and safety footwear (see Directive 89/686/EEC and standard EN ISO 20344). Wash body with soap and water after removing protective clothing.

##### EYE PROTECTION

Wear airtight protective goggles (see standard EN 166).

##### RESPIRATORY PROTECTION

If the threshold value (e.g. TLV-TWA) is exceeded for the substance or one of the substances present in the product, use a mask with a type B filter whose class (1, 2 or 3) must be chosen according to the limit of use concentration. (see standard EN 14387). In the presence of gases or vapours of various kinds and/or gases or vapours containing particulate (aerosol sprays, fumes, mists, etc.) combined filters are required.

Respiratory protection devices must be used if the technical measures adopted are not suitable for restricting the worker's exposure to the threshold values considered. The protection provided by masks is in any case limited.

If the substance considered is odourless or its olfactory threshold is higher than the corresponding TLV-TWA and in the case of an emergency, wear open-circuit compressed air breathing apparatus (in compliance with standard EN 137) or external air-intake breathing apparatus (in compliance with standard EN 138). For a correct choice of respiratory protection device, see standard EN 529.

##### ENVIRONMENTAL EXPOSURE CONTROLS.

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

### SECTION 9. Physical and chemical properties.

#### 9.1. Information on basic physical and chemical properties.

Appearance	viscous liquid
Colour	white
Odour	pungent
Odour threshold.	Not available.
pH.	Not available.
Melting point / freezing point.	Not available.
Initial boiling point.	Not available.
Boiling range.	Not available.
Flash point.	> 150 °C.
Evaporation Rate	Not available.

### SECTION 9. Physical and chemical properties. ... / >>

Flammability of solids and gases	Not available.
Lower inflammability limit.	Not available.
Upper inflammability limit.	Not available.
Lower explosive limit.	Not available.
Upper explosive limit.	Not available.
Vapour pressure.	Not available.
Vapour density	Not available.
Relative density.	Not available.
Solubility	immiscible with water
Partition coefficient: n-octanol/water	Not available.
Auto-ignition temperature.	> 400 °C.
Decomposition temperature.	Not available.
Viscosity	Not available.
Explosive properties	Not available.
Oxidising properties	Not available.

#### 9.2. Other information.

Information not available.

### SECTION 10. Stability and reactivity.

#### 10.1. Reactivity.

Information not available.

#### 10.2. Chemical stability.

Information not available.

#### 10.3. Possibility of hazardous reactions.

The product may react violently with water.

ACETIC ACID: risk of explosion on contact with: chromium (IV) oxide, potassium permanganate, sodium peroxide, perchloric acid, phosphorus chloride, hydrogen peroxide. Can react dangerously with: alcohols, bromine pentafluoride, chlorosulphuric acid, dichromate-sulphuric acid, ethane diamine, ethylene glycol, potassium hydroxide, strong bases, sodium hydroxide, strong oxidising agent, nitric acid, ammonium nitrate, potassium tert-butoxide, oleum. Forms explosive mixtures with air.

#### 10.4. Conditions to avoid.

Avoid overheating. Prevent moisture or water from penetrating inside the containers.

ACETIC ACID: avoid exposure to sources of heat and naked flames.

#### 10.5. Incompatible materials.

ACETIC ACID: carbonates, hydroxides, many oxides and phosphates. Oxidising substances and bases.

#### 10.6. Hazardous decomposition products.

Information not available.

### SECTION 11. Toxicological information.

Oral LD50 (Rat) >5000mg/kg; Dermal LD50 (Rabbit) >2000 mg/kg.

#### 11.1. Information on toxicological effects.

In the absence of experimental data for the product itself, health hazards are evaluated according to the properties of the substances it contains, using the criteria specified in the applicable regulation for classification.

It is therefore necessary to take into account the concentration of the individual hazardous substances indicated in section 3, to evaluate the toxicological effects of exposure to the product.

Acute effects: stinging eyes. Symptoms may include: rubescence, edema, pain and lachrymation. Ingestion may cause health problems, including stomach pain and sting, nausea and sickness.

Acute effects: contact with skin may cause: irritation, erythema, edema, dryness and chapped skin. Ingestion may cause health disorders, including stomach pain and sting, nausea and sickness.

ACETIC ACID	
LD50 (Oral).	3310 mg/kg Rat
LD50 (Dermal).	1060 mg/kg Rabbit
LC50 (Inhalation).	11.4 mg/l/4h Rat



# ACC Silicones LTD

## SILCOSET® 151

Revision nr.17  
Dated 07/12/2015  
Printed on 12/02/2016  
Page n. 6 / 8

EN

### SECTION 12. Ecological information.

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

#### 12.1. Toxicity.

Information not available.

#### 12.2. Persistence and degradability.

ACETIC ACID  
Solubility in water. > 10000 mg/l  
Rapidly biodegradable.

#### 12.3. Bioaccumulative potential.

ACETIC ACID  
Partition coefficient: n-octanol/water. -0.17

#### 12.4. Mobility in soil.

ACETIC ACID  
Partition coefficient: soil/water. 1.153

#### 12.5. Results of PBT and vPvB assessment.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

#### 12.6. Other adverse effects.

Information not available.

### SECTION 13. Disposal considerations.

#### 13.1. Waste treatment methods.

Reuse, when possible. Product residues should be considered special hazardous waste. The hazard level of waste containing this product should be evaluated according to applicable regulations.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

### SECTION 14. Transport information.

#### 14.1. UN number.

Not applicable.

#### 14.2. UN proper shipping name.

Not applicable.

#### 14.3. Transport hazard class(es).

Not applicable.

#### 14.4. Packing group.

Not applicable.

#### 14.5. Environmental hazards.

Not applicable.



# ACC Silicones LTD

## SILCOSET® 151

Revision nr.17  
Dated 07/12/2015  
Printed on 12/02/2016  
Page n. 7 / 8

EN

### SECTION 14. Transport information. ... / >>

#### 14.6. Special precautions for user.

Not applicable.

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code.

Information not relevant.

### SECTION 15. Regulatory information.

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture.

Seveso category. None.

Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006.

Product.  
Point. 3

Substances in Candidate List (Art. 59 REACH).

None.

Substances subject to authorisation (Annex XIV REACH).

None.

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None.

Substances subject to the Rotterdam Convention:

None.

Substances subject to the Stockholm Convention:

None.

Healthcare controls.

Workers exposed to this chemical agent must not undergo health checks, provided that available risk-assessment data prove that the risks related to the workers' health and safety are modest and that the 98/24/EC directive is respected.

#### 15.2. Chemical safety assessment.

No chemical safety assessment has been processed for the mixture and the substances it contains.

### SECTION 16. Other information.

Text of hazard (H) indications mentioned in section 2-3 of the sheet:

<b>Flam. Liq. 3</b>	Flammable liquid, category 3
<b>Acute Tox. 4</b>	Acute toxicity, category 4
<b>Skin Corr. 1A</b>	Skin corrosion, category 1A
<b>Skin Corr. 1B</b>	Skin corrosion, category 1B
<b>Eye Irrit. 2</b>	Eye irritation, category 2
<b>Skin Irrit. 2</b>	Skin irritation, category 2
<b>H226</b>	Flammable liquid and vapour.
<b>H302</b>	Harmful if swallowed.
<b>H314</b>	Causes severe skin burns and eye damage.
<b>H319</b>	Causes serious eye irritation.
<b>H315</b>	Causes skin irritation.
<b>EUH014</b>	Reacts violently with water.

#### LEGEND:

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals

### SECTION 16. Other information. ... / >>

- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

#### GENERAL BIBLIOGRAPHY

1. Regulation (EU) 1907/2006 (REACH) of the European Parliament
2. Regulation (EU) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
4. Regulation (EU) 2015/830 of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- ECHA website

#### Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.